

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749658

Luminaire Tested: LD4D50D010-EU4DR6540509030-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P749658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR6540509030-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4258.6 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P749658
CATALOG NUMBER: LD4D50D010-EU4DR6540509030-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P749658

CATALOG NUMBER: LD4D50D010-EU4DR6540509030-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225830
5°	225257
10°	225068
15°	218130
20°	198576
25°	173051
30°	143928
35°	114041
40°	82310
45°	52002
50°	27104
55°	14408
60°	7569
65°	4160
70°	1742
75°	1918
80°	1345
85°	1139

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 52002 cd/sqm



TEST NUMBER: P749658

CATALOG NUMBER: LD4D50D010-EU4DR6540509030-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.7	8.6
10°-20°	1001.3	23.5
20°-30°	1224.0	28.7
30°-40°	993.1	23.3
40°-50°	494.9	11.6
50°-60°	138.0	3.2
60°-70°	31.4	0.7
70°-80°	8.2	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2591.0	60.8
0°-40°	3584.0	84.2
0°-60°	4217.0	99.0
0°-90°	4258.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4258.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3867	
5°	3842	366
15°	3608	1001
25°	2685	1224
35°	1600	993
45°	630	495
55°	142	138
65°	30	31
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P749658

CATALOG NUMBER: LD4D50D010-EU4DR6540509030-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3866.7
2.5°	3863.8
5°	3842.2
7.5°	3829.7
10°	3795.1
12.5°	3724.6
15°	3607.6
17.5°	3424.6
20°	3195.0
22.5°	2947.3
25°	2685.4
27.5°	2405.2
30°	2134.2
32.5°	1866.6
35°	1599.5
37.5°	1333.0
40°	1079.6
42.5°	842.1
45°	629.6
47.5°	438.7
50°	298.3
52.5°	205.7
55°	141.5
57.5°	95.5
60°	64.8
62.5°	44.9
65°	30.1
67.5°	15.3
70°	10.2
72.5°	9.7
75°	8.5
77.5°	5.7
80°	4.0
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)