

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748953

Luminaire Tested: LD4D45BD010-EU4DR7040509027-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR7040509027-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2494.1 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748953
CATALOG NUMBER: LD4D45BD010-EU4DR7040509027-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P748953

CATALOG NUMBER: LD4D45BD010-EU4DR7040509027-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306367
5°	297261
10°	288971
15°	285186
20°	266300
25°	200063
30°	141429
35°	50099
40°	26344
45°	28060
50°	29050
55°	29602
60°	29784
65°	29163
70°	27505
75°	25498
80°	22651
85°	18428

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 29791 cd/sqm



TEST NUMBER: P748953

CATALOG NUMBER: LD4D45BD010-EU4DR7040509027-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.6	10.2
10°-20°	701.2	28.1
20°-30°	772.3	31.0
30°-40°	295.1	11.8
40°-50°	139.3	5.6
50°-60°	138.5	5.6
60°-70°	110.9	4.4
70°-80°	63.7	2.6
80°-90°	17.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1729.1	69.3
0°-40°	2024.2	81.2
0°-60°	2302.1	92.3
0°-90°	2494.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2494.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2804	
5°	2710	256
15°	2521	701
25°	1660	772
35°	376	295
45°	182	139
55°	155	139
65°	113	111
75°	60	64
85°	15	17
90°	0	



TEST NUMBER: P748953

CATALOG NUMBER: LD4D45BD010-EU4DR7040509027-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2804.0
2.5°	2774.7
5°	2710.3
7.5°	2656.6
10°	2604.6
12.5°	2560.7
15°	2521.2
17.5°	2425.7
20°	2290.3
22.5°	1998.2
25°	1659.5
27.5°	1444.6
30°	1121.0
32.5°	724.1
35°	375.6
37.5°	202.9
40°	184.7
42.5°	183.4
45°	181.6
47.5°	177.6
50°	170.9
52.5°	163.4
55°	155.4
57.5°	146.5
60°	136.3
62.5°	124.7
65°	112.8
67.5°	99.4
70°	86.1
72.5°	72.8
75°	60.4
77.5°	47.5
80°	36.0
82.5°	25.3
85°	14.7
87.5°	5.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)