

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749772

Luminaire Tested: LD4D50D010-EU4DR7040509040-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P749772
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR7040509040-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3191.9 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P749772

CATALOG NUMBER: LD4D50D010-EU4DR7040509040-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P749772

CATALOG NUMBER: LD4D50D010-EU4DR7040509040-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	392082
5°	380430
10°	369828
15°	364977
20°	340819
25°	256037
30°	180994
35°	64117
40°	33718
45°	35910
50°	37175
55°	37889
60°	38110
65°	37306
70°	35204
75°	32632
80°	28944
85°	23443

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 38128 cd/sqm



TEST NUMBER: P749772

CATALOG NUMBER: LD4D50D010-EU4DR7040509040-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.2	10.2
10°-20°	897.4	28.1
20°-30°	988.4	31.0
30°-40°	377.6	11.8
40°-50°	178.3	5.6
50°-60°	177.3	5.6
60°-70°	141.9	4.4
70°-80°	81.6	2.6
80°-90°	22.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2212.9	69.3
0°-40°	2590.6	81.2
0°-60°	2946.2	92.3
0°-90°	3191.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3191.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3588	
5°	3469	327
15°	3227	897
25°	2124	988
35°	481	378
45°	232	178
55°	199	177
65°	144	142
75°	77	82
85°	19	22
90°	0	



TEST NUMBER: P749772

CATALOG NUMBER: LD4D50D010-EU4DR7040509040-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3588.5
2.5°	3551.0
5°	3468.6
7.5°	3399.9
10°	3333.4
12.5°	3277.2
15°	3226.6
17.5°	3104.5
20°	2931.2
22.5°	2557.3
25°	2123.8
27.5°	1848.8
30°	1434.6
32.5°	926.7
35°	480.7
37.5°	259.7
40°	236.4
42.5°	234.7
45°	232.4
47.5°	227.3
50°	218.7
52.5°	209.1
55°	198.9
57.5°	187.5
60°	174.4
62.5°	159.7
65°	144.3
67.5°	127.3
70°	110.2
72.5°	93.2
75°	77.3
77.5°	60.8
80°	46.0
82.5°	32.4
85°	18.7
87.5°	7.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)