

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748979

Luminaire Tested: LD4D45BD010-EU4DR7040509035-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748979
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR7040509035-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2596.5 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748979
CATALOG NUMBER: LD4D45BD010-EU4DR7040509035-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P748979

CATALOG NUMBER: LD4D45BD010-EU4DR7040509035-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318943
5°	309468
10°	300842
15°	296893
20°	277241
25°	208272
30°	147233
35°	52153
40°	27428
45°	29204
50°	30239
55°	30821
60°	31008
65°	30352
70°	28655
75°	26553
80°	23532
85°	19180

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 31011 cd/sqm



TEST NUMBER: P748979

CATALOG NUMBER: LD4D45BD010-EU4DR7040509035-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.1	10.3
10°-20°	730.0	28.1
20°-30°	804.0	31.0
30°-40°	307.2	11.8
40°-50°	145.0	5.6
50°-60°	144.2	5.6
60°-70°	115.5	4.4
70°-80°	66.4	2.6
80°-90°	18.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1800.1	69.3
0°-40°	2107.3	81.2
0°-60°	2396.6	92.3
0°-90°	2596.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2596.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2919	
5°	2822	266
15°	2625	730
25°	1728	804
35°	391	307
45°	189	145
55°	162	144
65°	117	115
75°	63	66
85°	15	18
90°	0	



TEST NUMBER: P748979
CATALOG NUMBER: LD4D45BD010-EU4DR7040509035-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2919.1
2.5°	2888.6
5°	2821.6
7.5°	2765.7
10°	2711.6
12.5°	2665.9
15°	2624.7
17.5°	2525.4
20°	2384.4
22.5°	2080.3
25°	1727.6
27.5°	1503.9
30°	1167.0
32.5°	753.8
35°	391.0
37.5°	211.2
40°	192.3
42.5°	190.9
45°	189.0
47.5°	184.9
50°	177.9
52.5°	170.1
55°	161.8
57.5°	152.5
60°	141.9
62.5°	129.9
65°	117.4
67.5°	103.5
70°	89.7
72.5°	75.8
75°	62.9
77.5°	49.5
80°	37.4
82.5°	26.3
85°	15.3
87.5°	6.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)