

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750344

Luminaire Tested: LD4D55D010-EU4DR6055659024-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR6055659024-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3751.9 lumens
Efficiency: N/A
Efficacy: 64.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P750344

CATALOG NUMBER: LD4D55D010-EU4DR6055659024-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P750344

CATALOG NUMBER: LD4D55D010-EU4DR6055659024-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	486844
5°	498816
10°	504850
15°	480931
20°	424036
25°	342969
30°	231989
35°	116256
40°	18856
45°	18465
50°	18834
55°	19106
60°	19645
65°	20088
70°	20573
75°	20812
80°	20072
85°	16673

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 20812 cd/sqm



TEST NUMBER: P750344

CATALOG NUMBER: LD4D55D010-EU4DR6055659024-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	434.7	11.6
10°-20°	1176.1	31.3
20°-30°	1265.3	33.7
30°-40°	550.0	14.7
40°-50°	92.4	2.5
50°-60°	89.8	2.4
60°-70°	76.8	2.0
70°-80°	51.4	1.4
80°-90°	15.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2876.1	76.7
0°-40°	3426.1	91.3
0°-60°	3608.3	96.2
0°-90°	3751.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3751.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4456	
5°	4548	435
15°	4252	1176
25°	2845	1265
35°	872	550
45°	120	92
55°	100	90
65°	78	77
75°	49	51
85°	13	15
90°	0	



TEST NUMBER: P750344

CATALOG NUMBER: LD4D55D010-EU4DR6055659024-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4455.8
2.5°	4581.1
5°	4548.0
7.5°	4558.5
10°	4550.4
12.5°	4456.4
15°	4251.7
17.5°	3976.9
20°	3646.9
22.5°	3293.8
25°	2844.9
27.5°	2275.5
30°	1838.8
32.5°	1417.2
35°	871.6
37.5°	372.9
40°	132.2
42.5°	121.8
45°	119.5
47.5°	115.4
50°	110.8
52.5°	105.5
55°	100.3
57.5°	95.1
60°	89.9
62.5°	84.1
65°	77.7
67.5°	71.3
70°	64.4
72.5°	56.8
75°	49.3
77.5°	40.6
80°	31.9
82.5°	22.6
85°	13.3
87.5°	4.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)