

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750500

Luminaire Tested: LD4D55D010-EU4DR7055659024-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR7055659024-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2923.4 lumens
Efficiency: N/A
Efficacy: 50.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P750500

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P750500

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	359107
5°	348436
10°	338719
15°	334278
20°	312146
25°	234493
30°	165766
35°	58715
40°	30879
45°	32881
50°	34047
55°	34688
60°	34920
65°	34178
70°	32265
75°	29888
80°	26553
85°	21562

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 34920 cd/sqm



TEST NUMBER: P750500

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	299.6	10.3
10°-20°	821.9	28.1
20°-30°	905.2	31.0
30°-40°	345.9	11.8
40°-50°	163.3	5.6
50°-60°	162.3	5.6
60°-70°	130.0	4.4
70°-80°	74.7	2.6
80°-90°	20.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2026.8	69.3
0°-40°	2372.6	81.2
0°-60°	2698.3	92.3
0°-90°	2923.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2923.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3287	
5°	3177	300
15°	2955	822
25°	1945	905
35°	440	346
45°	213	163
55°	182	162
65°	132	130
75°	71	75
85°	17	20
90°	0	



TEST NUMBER: P750500

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3286.7
2.5°	3252.3
5°	3176.9
7.5°	3113.9
10°	3053.0
12.5°	3001.5
15°	2955.2
17.5°	2843.3
20°	2684.6
22.5°	2342.2
25°	1945.1
27.5°	1693.3
30°	1313.9
32.5°	848.7
35°	440.2
37.5°	237.8
40°	216.5
42.5°	214.9
45°	212.8
47.5°	208.1
50°	200.3
52.5°	191.5
55°	182.1
57.5°	171.7
60°	159.8
62.5°	146.2
65°	132.2
67.5°	116.6
70°	101.0
72.5°	85.3
75°	70.8
77.5°	55.7
80°	42.2
82.5°	29.7
85°	17.2
87.5°	6.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)