

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748850

Luminaire Tested: LD4D45BD010-EU4DR6040509050-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6040509050-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3957.3 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748850
CATALOG NUMBER: LD4D45BD010-EU4DR6040509050-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P748850

CATALOG NUMBER: LD4D45BD010-EU4DR6040509050-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	513504
5°	526137
10°	532487
15°	507264
20°	447255
25°	361752
30°	244694
35°	122619
40°	19897
45°	19469
50°	19854
55°	20154
60°	20716
65°	21200
70°	21691
75°	21952
80°	21141
85°	17676

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 21952 cd/sqm



TEST NUMBER: P748850

CATALOG NUMBER: LD4D45BD010-EU4DR6040509050-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	458.5	11.6
10°-20°	1240.4	31.3
20°-30°	1334.6	33.7
30°-40°	580.1	14.7
40°-50°	97.4	2.5
50°-60°	94.7	2.4
60°-70°	81.0	2.0
70°-80°	54.2	1.4
80°-90°	16.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3033.5	76.7
0°-40°	3613.7	91.3
0°-60°	3805.8	96.2
0°-90°	3957.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3957.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4700	
5°	4797	458
15°	4484	1240
25°	3001	1335
35°	919	580
45°	126	97
55°	106	95
65°	82	81
75°	52	54
85°	14	16
90°	0	



TEST NUMBER: P748850

CATALOG NUMBER: LD4D45BD010-EU4DR6040509050-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4699.8
2.5°	4831.9
5°	4797.1
7.5°	4808.1
10°	4799.5
12.5°	4700.4
15°	4484.5
17.5°	4194.6
20°	3846.6
22.5°	3474.1
25°	3000.7
27.5°	2400.1
30°	1939.5
32.5°	1494.8
35°	919.3
37.5°	393.3
40°	139.5
42.5°	128.4
45°	126.0
47.5°	121.7
50°	116.8
52.5°	111.3
55°	105.8
57.5°	100.3
60°	94.8
62.5°	88.7
65°	82.0
67.5°	75.2
70°	67.9
72.5°	59.9
75°	52.0
77.5°	42.8
80°	33.6
82.5°	23.9
85°	14.1
87.5°	4.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)