

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748917

Luminaire Tested: LD4D45BD010-EU4DR6540509050-4LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748917  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D45BD010-EU4DR6540509050-4LBCSSQMMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3863.0 lumens  
Efficiency: N/A  
Efficacy: 99.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P748917  
CATALOG NUMBER: LD4D45BD010-EU4DR6540509050-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P748917  
 CATALOG NUMBER: LD4D45BD010-EU4DR6540509050-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	204852
5°	204338
10°	204163
15°	197869
20°	180135
25°	156980
30°	130562
35°	103453
40°	74663
45°	47170
50°	24587
55°	13064
60°	6868
65°	3773
70°	1588
75°	1738
80°	1211
85°	1005

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 47170 cd/sqm



TEST NUMBER: P748917

CATALOG NUMBER: LD4D45BD010-EU4DR6540509050-4LBCSSQMMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	331.7	8.6
10°-20°	908.3	23.5
20°-30°	1110.3	28.7
30°-40°	900.9	23.3
40°-50°	448.9	11.6
50°-60°	125.2	3.2
60°-70°	28.4	0.7
70°-80°	7.4	0.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2350.3	60.8
0°-40°	3251.2	84.2
0°-60°	3825.3	99.0
0°-90°	3863.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3863.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3508	
5°	3485	332
15°	3272	908
25°	2436	1110
35°	1451	901
45°	571	449
55°	128	125
65°	27	28
75°	8	7
85°	2	2
90°	0	



TEST NUMBER: P748917

CATALOG NUMBER: LD4D45BD010-EU4DR6540509050-4LBCSSQMMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3507.5
2.5°	3505.0
5°	3485.4
7.5°	3474.0
10°	3442.6
12.5°	3378.7
15°	3272.5
17.5°	3106.5
20°	2898.3
22.5°	2673.6
25°	2436.0
27.5°	2181.8
30°	1936.0
32.5°	1693.2
35°	1451.0
37.5°	1209.2
40°	979.3
42.5°	763.9
45°	571.1
47.5°	397.9
50°	270.6
52.5°	186.6
55°	128.3
57.5°	86.6
60°	58.8
62.5°	40.7
65°	27.3
67.5°	13.9
70°	9.3
72.5°	8.8
75°	7.7
77.5°	5.2
80°	3.6
82.5°	2.6
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)