

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749801

Luminaire Tested: LD4D55D010-EU4DR2555659027-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P749801
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR2555659027-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4364.9 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P749801

CATALOG NUMBER: LD4D55D010-EU4DR2555659027-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P749801

CATALOG NUMBER: LD4D55D010-EU4DR2555659027-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99 | 99 | 98 | 96 | | | | | | | | | | | | | | | | | | | |
| 2 | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98 | 99 | 97 | 96 | 97 | 95 | 94 | 92 | | | | | | | | | | | | | | | | | | | |
| 3 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 98 | 95 | 93 | 96 | 93 | 91 | 94 | 92 | 90 | 89 | | | | | | | | | | | | | | | | | | | |
| 4 | 103 | 97 | 93 | 90 | 102 | 96 | 93 | 90 | 94 | 91 | 89 | 93 | 90 | 88 | 91 | 89 | 87 | 85 | | | | | | | | | | | | | | | | | | | |
| 5 | 100 | 93 | 89 | 86 | 98 | 93 | 89 | 86 | 91 | 87 | 85 | 89 | 86 | 84 | 88 | 85 | 83 | 82 | | | | | | | | | | | | | | | | | | | |
| 6 | 97 | 90 | 85 | 82 | 95 | 89 | 85 | 82 | 88 | 84 | 81 | 87 | 83 | 81 | 85 | 83 | 80 | 79 | | | | | | | | | | | | | | | | | | | |
| 7 | 93 | 87 | 82 | 79 | 92 | 86 | 82 | 79 | 85 | 81 | 78 | 84 | 80 | 78 | 83 | 80 | 78 | 77 | | | | | | | | | | | | | | | | | | | |
| 8 | 91 | 84 | 79 | 76 | 90 | 83 | 79 | 76 | 82 | 78 | 76 | 81 | 78 | 75 | 80 | 77 | 75 | 74 | | | | | | | | | | | | | | | | | | | |
| 9 | 88 | 81 | 76 | 73 | 87 | 80 | 76 | 73 | 80 | 76 | 73 | 79 | 75 | 73 | 78 | 75 | 73 | 72 | | | | | | | | | | | | | | | | | | | |
| 10 | 85 | 78 | 74 | 71 | 85 | 78 | 74 | 71 | 77 | 73 | 71 | 76 | 73 | 71 | 76 | 73 | 70 | 69 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1808812 |
| 5° | 1684678 |
| 10° | 1201726 |
| 15° | 707772 |
| 20° | 440383 |
| 25° | 241678 |
| 30° | 110532 |
| 35° | 41856 |
| 40° | 18955 |
| 45° | 11403 |
| 50° | 4725 |
| 55° | 3048 |
| 60° | 2120 |
| 65° | 1448 |
| 70° | 224 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11403 cd/sqm



TEST NUMBER: P749801

CATALOG NUMBER: LD4D55D010-EU4DR2555659027-4LBCSSQMMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1320.1 | 30.2 |
| 10°-20° | 1788.0 | 41.0 |
| 20°-30° | 946.2 | 21.7 |
| 30°-40° | 233.6 | 5.4 |
| 40°-50° | 57.0 | 1.3 |
| 50°-60° | 15.0 | 0.3 |
| 60°-70° | 5.0 | 0.1 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 4054.2 | 92.9 |
| 0°-40° | 4287.8 | 98.2 |
| 0°-60° | 4359.7 | 99.9 |
| 0°-90° | 4364.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 4364.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 16555 | |
| 5° | 15360 | ### |
| 15° | 6257 | 1788 |
| 25° | 2005 | 946 |
| 35° | 314 | 234 |
| 45° | 74 | 57 |
| 55° | 16 | 15 |
| 65° | 6 | 5 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P749801

CATALOG NUMBER: LD4D55D010-EU4DR2555659027-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 16555.0 |
| 2.5° | 16282.9 |
| 5° | 15360.2 |
| 7.5° | 13506.5 |
| 10° | 10831.6 |
| 12.5° | 8188.1 |
| 15° | 6257.1 |
| 17.5° | 4876.5 |
| 20° | 3787.5 |
| 22.5° | 2840.5 |
| 25° | 2004.7 |
| 27.5° | 1344.4 |
| 30° | 876.1 |
| 32.5° | 533.0 |
| 35° | 313.8 |
| 37.5° | 192.1 |
| 40° | 132.9 |
| 42.5° | 101.6 |
| 45° | 73.8 |
| 47.5° | 44.5 |
| 50° | 27.8 |
| 52.5° | 20.2 |
| 55° | 16.0 |
| 57.5° | 12.5 |
| 60° | 9.7 |
| 62.5° | 7.7 |
| 65° | 5.6 |
| 67.5° | 2.1 |
| 70° | 0.7 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)