

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740147

Luminaire Tested: LD4D05D010-EU4DR350210IC9024-4LBCSSQMB

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P740147
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR350210IC9024-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 509.5 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740147

CATALOG NUMBER: LD4D05D010-EU4DR350210IC9024-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P740147

CATALOG NUMBER: LD4D05D010-EU4DR350210IC9024-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	98	96	96	96	92	92																	
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	96	92	91	91	89	89	89	84	84																	
	2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	92	89	89	89	84	84	84	81	81																	
	3	106	101	97	94	105	100	96	93	97	94	92	95	93	91	93	91	89	88	88	88	84	84	84	81	81	81	78	78																	
	4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84	84	84	81	81	81	78	78	78	75	75																	
	5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81	81	81	79	79	79	76	76	76	72	72																	
	6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78	78	78	75	75	75	72	72	72	69	69																	
	7	93	85	81	77	91	85	80	77	84	80	77	83	79	77	82	79	76	75	75	75	72	72	72	69	69	69	66	66																	
	8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72	72	72	69	69	69	66	66	66	63	63																	
	9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70	70	70	67	67	67	64	64	64	61	61																	
	10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68	68	68	65	65	65	62	62	62	59	59																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153173
5°	149579
10°	134811
15°	104631
20°	59346
25°	23086
30°	8617
35°	4722
40°	3095
45°	1870
50°	1190
55°	838
60°	612
65°	336
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1870 cd/sqm



TEST NUMBER: P740147

CATALOG NUMBER: LD4D05D010-EU4DR350210IC9024-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.4	24.6
10°-20°	244.9	48.1
20°-30°	99.9	19.6
30°-40°	23.9	4.7
40°-50°	10.0	2.0
50°-60°	4.1	0.8
60°-70°	1.3	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	470.2	92.3
0°-40°	494.1	97.0
0°-60°	508.2	99.7
0°-90°	509.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	509.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1402	
5°	1364	125
15°	925	245
25°	192	100
35°	35	24
45°	12	10
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P740147

CATALOG NUMBER: LD4D05D010-EU4DR350210IC9024-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1401.9
2.5°	1393.5
5°	1363.8
7.5°	1304.4
10°	1215.1
12.5°	1089.2
15°	925.0
17.5°	724.2
20°	510.4
22.5°	325.4
25°	191.5
27.5°	108.2
30°	68.3
32.5°	48.0
35°	35.4
37.5°	27.4
40°	21.7
42.5°	16.7
45°	12.1
47.5°	9.1
50°	7.0
52.5°	5.6
55°	4.4
57.5°	3.6
60°	2.8
62.5°	2.1
65°	1.3
67.5°	0.5
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)