

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751280

Luminaire Tested: LD4D60D010-EU4DR7055659024-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P751280  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D60D010-EU4DR7055659024-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3214.6 lumens  
Efficiency: N/A  
Efficacy: 49.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P751280

CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P751280

CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	394890
5°	383150
10°	372469
15°	367579
20°	343249
25°	257869
30°	182294
35°	64571
40°	33946
45°	36157
50°	37446
55°	38155
60°	38394
65°	37565
70°	35460
75°	32843
80°	29132
85°	23694

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 38394 cd/sqm



TEST NUMBER: P751280

CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	329.5	10.3
10°-20°	903.8	28.1
20°-30°	995.4	31.0
30°-40°	380.3	11.8
40°-50°	179.6	5.6
50°-60°	178.5	5.6
60°-70°	142.9	4.4
70°-80°	82.1	2.6
80°-90°	22.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2228.8	69.3
0°-40°	2609.1	81.2
0°-60°	2967.2	92.3
0°-90°	3214.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3214.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3614	
5°	3493	330
15°	3250	904
25°	2139	995
35°	484	380
45°	234	180
55°	200	179
65°	145	143
75°	78	82
85°	19	22
90°	0	



TEST NUMBER: P751280

CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3614.2
2.5°	3576.4
5°	3493.4
7.5°	3424.2
10°	3357.2
12.5°	3300.6
15°	3249.6
17.5°	3126.6
20°	2952.1
22.5°	2575.6
25°	2139.0
27.5°	1862.0
30°	1444.9
32.5°	933.3
35°	484.1
37.5°	261.5
40°	238.0
42.5°	236.3
45°	234.0
47.5°	228.9
50°	220.3
52.5°	210.6
55°	200.3
57.5°	188.8
60°	175.7
62.5°	160.8
65°	145.3
67.5°	128.2
70°	111.0
72.5°	93.8
75°	77.8
77.5°	61.2
80°	46.3
82.5°	32.6
85°	18.9
87.5°	7.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)