

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751282

Luminaire Tested: LD4D60D010-EU4DR7055659027-4LBCSSQMB

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P751282  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D60D010-EU4DR7055659027-4LBCSSQMB  
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5798.3 lumens  
Efficiency: N/A  
Efficacy: 90.0 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P751282  
CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P751282

CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93	
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78	
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71	71	
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60	
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56	56	
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48	48	
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44	44	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	500032
5°	498783
10°	497705
15°	497559
20°	492695
25°	462826
30°	412618
35°	328975
40°	218438
45°	130599
50°	67703
55°	35584
60°	12587
65°	207
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 130599 cd/sqm



TEST NUMBER: P751282

CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	432.5	7.5
10°-20°	1240.4	21.4
20°-30°	1749.8	30.2
30°-40°	1510.5	26.1
40°-50°	676.5	11.7
50°-60°	177.1	3.1
60°-70°	11.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3422.7	59.0
0°-40°	4933.2	85.1
0°-60°	5786.7	99.8
0°-90°	5798.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5798.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4576	
5°	4548	432
15°	4399	1240
25°	3839	1750
35°	2466	1511
45°	845	676
55°	187	177
65°	1	12
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751282  
CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4576.5
2.5°	4571.6
5°	4547.7
7.5°	4528.0
10°	4486.0
12.5°	4448.1
15°	4398.7
17.5°	4342.0
20°	4237.4
22.5°	4065.4
25°	3839.1
27.5°	3576.6
30°	3270.5
32.5°	2896.0
35°	2466.4
37.5°	1992.4
40°	1531.5
42.5°	1163.7
45°	845.2
47.5°	582.7
50°	398.3
52.5°	274.9
55°	186.8
57.5°	112.7
60°	57.6
62.5°	18.1
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)