

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751151

Luminaire Tested: LD4D60D010-EU4DR6055659030-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751151
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6055659030-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5423.7 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751151
CATALOG NUMBER: LD4D60D010-EU4DR6055659030-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P751151

CATALOG NUMBER: LD4D60D010-EU4DR6055659030-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	703781
5°	721090
10°	729805
15°	695239
20°	612979
25°	495798
30°	335368
35°	168049
40°	27257
45°	26685
50°	27214
55°	27621
60°	28386
65°	29033
70°	29710
75°	30099
80°	29006
85°	24195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 30099 cd/sqm



TEST NUMBER: P751151

CATALOG NUMBER: LD4D60D010-EU4DR6055659030-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	628.4	11.6
10°-20°	1700.1	31.3
20°-30°	1829.2	33.7
30°-40°	795.1	14.7
40°-50°	133.5	2.5
50°-60°	129.9	2.4
60°-70°	111.1	2.0
70°-80°	74.3	1.4
80°-90°	22.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4157.6	76.7
0°-40°	4952.7	91.3
0°-60°	5216.1	96.2
0°-90°	5423.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5423.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6441	
5°	6575	628
15°	6146	1700
25°	4113	1829
35°	1260	795
45°	173	134
55°	145	130
65°	112	111
75°	71	74
85°	19	22
90°	0	



TEST NUMBER: P751151

CATALOG NUMBER: LD4D60D010-EU4DR6055659030-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6441.3
2.5°	6622.4
5°	6574.6
7.5°	6589.7
10°	6578.0
12.5°	6442.2
15°	6146.3
17.5°	5748.9
20°	5271.9
22.5°	4761.4
25°	4112.6
27.5°	3289.4
30°	2658.2
32.5°	2048.8
35°	1259.9
37.5°	539.0
40°	191.1
42.5°	176.0
45°	172.7
47.5°	166.8
50°	160.1
52.5°	152.6
55°	145.0
57.5°	137.5
60°	129.9
62.5°	121.6
65°	112.3
67.5°	103.1
70°	93.0
72.5°	82.2
75°	71.3
77.5°	58.7
80°	46.1
82.5°	32.7
85°	19.3
87.5°	6.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)