

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740575

Luminaire Tested: LD4D05D010-EU4DR600210IC9030-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P740575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR600210IC9030-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 572.8 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740575
CATALOG NUMBER: LD4D05D010-EU4DR600210IC9030-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P740575

CATALOG NUMBER: LD4D05D010-EU4DR600210IC9030-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74330
5°	76150
10°	77074
15°	73423
20°	64729
25°	52357
30°	35414
35°	17740
40°	2881
45°	2812
50°	2873
55°	2915
60°	2994
65°	3077
70°	3163
75°	3166
80°	3083
85°	2633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 3166 cd/sqm



TEST NUMBER: P740575
 CATALOG NUMBER: LD4D05D010-EU4DR600210IC9030-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.4	11.6
10°-20°	179.5	31.3
20°-30°	193.2	33.7
30°-40°	84.0	14.7
40°-50°	14.1	2.5
50°-60°	13.7	2.4
60°-70°	11.7	2.0
70°-80°	7.9	1.4
80°-90°	2.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.1	76.7
0°-40°	523.0	91.3
0°-60°	550.8	96.2
0°-90°	572.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	572.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	680	
5°	694	66
15°	649	180
25°	434	193
35°	133	84
45°	18	14
55°	15	14
65°	12	12
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P740575
CATALOG NUMBER: LD4D05D010-EU4DR600210IC9030-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	680.3
2.5°	699.3
5°	694.3
7.5°	695.9
10°	694.7
12.5°	680.3
15°	649.1
17.5°	607.1
20°	556.7
22.5°	502.8
25°	434.3
27.5°	347.4
30°	280.7
32.5°	216.3
35°	133.0
37.5°	57.0
40°	20.2
42.5°	18.6
45°	18.2
47.5°	17.6
50°	16.9
52.5°	16.1
55°	15.3
57.5°	14.5
60°	13.7
62.5°	12.8
65°	11.9
67.5°	10.9
70°	9.9
72.5°	8.7
75°	7.5
77.5°	6.2
80°	4.9
82.5°	3.4
85°	2.1
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)