

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739886

Luminaire Tested: LD4D05D010-EU4DR150210IC9035-4LBSQW1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P739886  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D05D010-EU4DR150210IC9035-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 615.3 lumens  
Efficiency: N/A  
Efficacy: 82.0 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P739886  
CATALOG NUMBER: LD4D05D010-EU4DR150210IC9035-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P739886

CATALOG NUMBER: LD4D05D010-EU4DR150210IC9035-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98					98			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96					96			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94					94			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93					93			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92					92			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90					90			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89					89			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88					88			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87					87			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86					86			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	943367	943367	943367
5°	554365	547190	551520
10°	165453	166610	169157
15°	41153	41961	40658
20°	12314	14262	12576
25°	4339	5531	4394
30°	1595	2097	1625
35°	799	900	770
40°	504	554	504
45°	371	399	371
50°	299	299	299
55°	244	244	244
60°	197	197	197
65°	150	150	150
70°	132	132	132
75°	83	83	106
80°	55	55	55
85°	33	33	33

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 399 cd/sqm



TEST NUMBER: P739886

CATALOG NUMBER: LD4D05D010-EU4DR150210IC9035-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	399.1	64.9
10°-20°	164.2	26.7
20°-30°	32.6	5.3
30°-40°	8.1	1.3
40°-50°	4.3	0.7
50°-60°	3.2	0.5
60°-70°	2.2	0.4
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.9	96.8
0°-40°	604.0	98.2
0°-60°	611.4	99.4
0°-90°	615.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	8384	8384	8384	8384	8384	
5°	5455	5399	5384	5421	5427	398
15°	474	483	483	474	468	162
25°	56	63	71	63	56	29
35°	11	12	12	12	11	7
45°	5	5	6	5	5	4
55°	4	4	4	4	4	3
65°	2	2	2	2	2	2
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P739886

CATALOG NUMBER: LD4D05D010-EU4DR150210IC9035-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	8384.0	8384.0	8384.0	8384.0	8384.0
2.5°	7562.7	7569.1	7571.6	7579.0	7606.7
5°	5454.8	5398.7	5384.2	5421.4	5426.8
7.5°	3231.2	3242.6	3284.1	3293.3	3260.0
10°	1773.2	1787.7	1785.6	1798.4	1812.9
12.5°	906.8	895.5	891.9	906.5	886.2
15°	473.8	482.7	483.1	474.5	468.1
17.5°	254.8	265.1	282.2	268.3	247.0
20°	150.5	159.7	174.3	162.9	153.7
22.5°	93.0	100.4	110.7	101.9	94.4
25°	55.7	63.2	71.0	62.8	56.4
27.5°	33.0	39.4	44.4	39.0	32.7
30°	21.3	24.8	28.0	24.5	21.7
32.5°	14.9	16.3	17.7	16.3	14.9
35°	11.0	11.7	12.4	11.7	10.6
37.5°	8.5	9.2	9.6	8.9	8.2
40°	7.1	7.5	7.8	7.5	7.1
42.5°	6.0	6.4	6.4	6.4	6.0
45°	5.3	5.3	5.7	5.3	5.3
47.5°	4.6	4.6	5.0	4.6	4.6
50°	4.3	4.3	4.3	4.3	4.3
52.5°	3.9	3.9	3.9	3.9	3.9
55°	3.5	3.5	3.5	3.5	3.5
57.5°	3.2	3.2	3.2	3.2	3.2
60°	2.8	2.8	2.8	2.8	2.8
62.5°	2.5	2.5	2.5	2.5	2.5
65°	2.1	2.1	2.1	2.1	2.1
67.5°	2.1	2.1	2.1	2.1	2.1
70°	1.8	1.8	1.8	1.8	1.8
72.5°	1.4	1.4	1.4	1.4	1.4
75°	1.1	1.1	1.1	1.1	1.4
77.5°	1.1	1.1	1.1	1.1	1.1
80°	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7
85°	0.4	0.4	0.4	0.4	0.4
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)