

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751164

Luminaire Tested: LD4D60D010-EU4DR6055659035-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751164
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6055659035-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5480.8 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751164
CATALOG NUMBER: LD4D60D010-EU4DR6055659035-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P751164

CATALOG NUMBER: LD4D60D010-EU4DR6055659035-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	711200
5°	728690
10°	737493
15°	702558
20°	619444
25°	501018
30°	338900
35°	169823
40°	27542
45°	26963
50°	27503
55°	27907
60°	28692
65°	29343
70°	30029
75°	30395
80°	29321
85°	24446

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 30395 cd/sqm



TEST NUMBER: P751164

CATALOG NUMBER: LD4D60D010-EU4DR6055659035-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	635.0	11.6
10°-20°	1718.0	31.3
20°-30°	1848.4	33.7
30°-40°	803.5	14.7
40°-50°	135.0	2.5
50°-60°	131.2	2.4
60°-70°	112.2	2.0
70°-80°	75.1	1.4
80°-90°	22.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4201.4	76.7
0°-40°	5004.9	91.3
0°-60°	5271.0	96.2
0°-90°	5480.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5480.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6509	
5°	6644	635
15°	6211	1718
25°	4156	1848
35°	1273	803
45°	174	135
55°	146	131
65°	114	112
75°	72	75
85°	20	22
90°	0	



TEST NUMBER: P751164

CATALOG NUMBER: LD4D60D010-EU4DR6055659035-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6509.2
2.5°	6692.2
5°	6643.9
7.5°	6659.1
10°	6647.3
12.5°	6510.0
15°	6211.0
17.5°	5809.5
20°	5327.5
22.5°	4811.6
25°	4155.9
27.5°	3324.1
30°	2686.2
32.5°	2070.3
35°	1273.2
37.5°	544.7
40°	193.1
42.5°	177.9
45°	174.5
47.5°	168.6
50°	161.8
52.5°	154.2
55°	146.5
57.5°	138.9
60°	131.3
62.5°	122.8
65°	113.5
67.5°	104.2
70°	94.0
72.5°	83.0
75°	72.0
77.5°	59.3
80°	46.6
82.5°	33.0
85°	19.5
87.5°	6.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)