

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740743

Luminaire Tested: LD4D05D010-EU4DR700210IC9035-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P740743  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D05D010-EU4DR700210IC9035-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 418.2 lumens  
Efficiency: N/A  
Efficacy: 55.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P740743  
CATALOG NUMBER: LD4D05D010-EU4DR700210IC9035-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P740743  
 CATALOG NUMBER: LD4D05D010-EU4DR700210IC9035-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	51374
5°	49849
10°	48461
15°	47825
20°	44660
25°	33551
30°	23719
35°	8403
40°	4422
45°	4697
50°	4861
55°	4972
60°	5004
65°	4886
70°	4600
75°	4264
80°	3775
85°	3134

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 5004 cd/sqm



TEST NUMBER: P740743

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9035-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.9	10.2
10°-20°	117.6	28.1
20°-30°	129.5	31.0
30°-40°	49.5	11.8
40°-50°	23.4	5.6
50°-60°	23.2	5.6
60°-70°	18.6	4.4
70°-80°	10.7	2.6
80°-90°	2.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.0	69.3
0°-40°	339.4	81.2
0°-60°	386.1	92.3
0°-90°	418.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	418.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	470	
5°	454	43
15°	423	118
25°	278	130
35°	63	49
45°	30	23
55°	26	23
65°	19	19
75°	10	11
85°	2	3
90°	0	



TEST NUMBER: P740743

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9035-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	470.2
2.5°	465.3
5°	454.5
7.5°	445.5
10°	436.8
12.5°	429.4
15°	422.8
17.5°	406.8
20°	384.1
22.5°	335.1
25°	278.3
27.5°	242.2
30°	188.0
32.5°	121.4
35°	63.0
37.5°	34.0
40°	31.0
42.5°	30.8
45°	30.4
47.5°	29.8
50°	28.6
52.5°	27.4
55°	26.1
57.5°	24.6
60°	22.9
62.5°	20.9
65°	18.9
67.5°	16.7
70°	14.4
72.5°	12.2
75°	10.1
77.5°	8.0
80°	6.0
82.5°	4.2
85°	2.5
87.5°	1.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)