

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739976

Luminaire Tested: LD4D05D010-EU4DR200210IC9040-4LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P739976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR200210IC9040-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 583.9 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739976
CATALOG NUMBER: LD4D05D010-EU4DR200210IC9040-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P739976

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9040-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97	94															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	98	96	95	94															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	95	93	92	91															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	93	91	89	88															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	91	88	86	85															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	88	86	84	83															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	86	84	82	81															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	84	82	80	79															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	82	80	78	77															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	81	78	76	75															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	363095
5°	327576
10°	183860
15°	93456
20°	39568
25°	18264
30°	9664
35°	5215
40°	2781
45°	1653
50°	952
55°	514
60°	328
65°	233
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1653 cd/sqm



TEST NUMBER: P739976

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9040-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.6	40.5
10°-20°	233.0	39.9
20°-30°	76.1	13.0
30°-40°	25.9	4.4
40°-50°	8.7	1.5
50°-60°	2.6	0.5
60°-70°	0.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.7	93.5
0°-40°	571.6	97.9
0°-60°	583.0	99.8
0°-90°	583.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	583.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3323	
5°	2987	237
15°	826	233
25°	152	76
35°	39	26
45°	11	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P739976

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9040-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3323.2
0.5°	3323.2
1°	3319.0
1.5°	3310.8
2°	3295.7
2.5°	3275.5
3°	3247.1
3.5°	3207.5
4°	3148.6
4.5°	3077.0
5°	2986.7
5.5°	2868.1
6°	2746.4
6.5°	2607.1
7°	2470.6
7.5°	2310.8
8°	2168.2
8.5°	2024.7
9°	1892.1
9.5°	1770.5
10°	1657.2
12.5°	1189.9
15°	826.2
17.5°	539.8
20°	340.3
22.5°	220.5
25°	151.5
27.5°	106.5
30°	76.6
32.5°	55.0
35°	39.1
37.5°	27.2
40°	19.5
42.5°	14.2
45°	10.7
47.5°	8.3
50°	5.6
52.5°	3.6
55°	2.7
57.5°	2.1
60°	1.5
62.5°	1.2
65°	0.9



TEST NUMBER: P739976
CATALOG NUMBER: LD4D05D010-EU4DR200210IC9040-4LBSQW1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.6
70°		0.3

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)