

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751245

Luminaire Tested: LD4D60D010-EU4DR6555659040-4LBCSSQMW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P751245  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D60D010-EU4DR6555659040-4LBCSSQMW  
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5704.9 lumens  
Efficiency: N/A  
Efficacy: 88.6 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P751245  
CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P751245

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	302526
5°	301765
10°	301506
15°	292211
20°	266023
25°	231822
30°	192808
35°	152777
40°	110267
45°	69661
50°	36308
55°	19296
60°	10139
65°	5569
70°	2339
75°	2572
80°	1783
85°	1541

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 69661 cd/sqm



TEST NUMBER: P751245

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBCSSQMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	489.9	8.6
10°-20°	1341.4	23.5
20°-30°	1639.7	28.7
30°-40°	1330.4	23.3
40°-50°	662.9	11.6
50°-60°	184.9	3.2
60°-70°	42.0	0.7
70°-80°	10.9	0.2
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3470.9	60.8
0°-40°	4801.3	84.2
0°-60°	5649.2	99.0
0°-90°	5704.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5704.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5180	
5°	5147	490
15°	4833	1341
25°	3597	1640
35°	2143	1330
45°	843	663
55°	190	185
65°	40	42
75°	11	11
85°	2	3
90°	0	



TEST NUMBER: P751245

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5179.9
2.5°	5176.1
5°	5147.2
7.5°	5130.4
10°	5084.0
12.5°	4989.6
15°	4832.8
17.5°	4587.7
20°	4280.2
22.5°	3948.3
25°	3597.4
27.5°	3222.1
30°	2859.0
32.5°	2500.5
35°	2142.8
37.5°	1785.8
40°	1446.3
42.5°	1128.1
45°	843.4
47.5°	587.6
50°	399.6
52.5°	275.6
55°	189.5
57.5°	127.9
60°	86.8
62.5°	60.1
65°	40.3
67.5°	20.6
70°	13.7
72.5°	12.9
75°	11.4
77.5°	7.6
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)