

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751346

Luminaire Tested: LD4D60D010-EU4DR7055659050-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751346
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR7055659050-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5322.8 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751346

CATALOG NUMBER: LD4D60D010-EU4DR7055659050-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P751346

CATALOG NUMBER: LD4D60D010-EU4DR7055659050-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	653849
5°	634422
10°	616739
15°	608649
20°	568353
25°	426973
30°	301833
35°	106920
40°	56225
45°	59876
50°	62009
55°	63167
60°	63568
65°	62229
70°	58716
75°	54415
80°	48260
85°	39239

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 63588 cd/sqm



TEST NUMBER: P751346

CATALOG NUMBER: LD4D60D010-EU4DR7055659050-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	545.6	10.3
10°-20°	1496.5	28.1
20°-30°	1648.2	31.0
30°-40°	629.8	11.8
40°-50°	297.3	5.6
50°-60°	295.6	5.6
60°-70°	236.7	4.4
70°-80°	136.0	2.6
80°-90°	37.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3690.4	69.3
0°-40°	4320.1	81.2
0°-60°	4913.1	92.3
0°-90°	5322.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5322.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5984	
5°	5784	546
15°	5381	1497
25°	3542	1648
35°	802	630
45°	388	297
55°	332	296
65°	241	237
75°	129	136
85°	31	37
90°	0	



TEST NUMBER: P751346

CATALOG NUMBER: LD4D60D010-EU4DR7055659050-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5984.3
2.5°	5921.8
5°	5784.4
7.5°	5669.8
10°	5558.9
12.5°	5465.1
15°	5380.8
17.5°	5177.1
20°	4888.1
22.5°	4264.7
25°	3541.7
27.5°	3083.1
30°	2392.4
32.5°	1545.4
35°	801.6
37.5°	433.0
40°	394.2
42.5°	391.3
45°	387.5
47.5°	379.0
50°	364.8
52.5°	348.7
55°	331.6
57.5°	312.7
60°	290.9
62.5°	266.2
65°	240.7
67.5°	212.2
70°	183.8
72.5°	155.4
75°	128.9
77.5°	101.4
80°	76.7
82.5°	54.0
85°	31.3
87.5°	12.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)