

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749280

Luminaire Tested: LD4D50D010-EU4DR4040509035-4LBCSSQMB

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P749280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR4040509035-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4813.5 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P749280
CATALOG NUMBER: LD4D50D010-EU4DR4040509035-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P749280
 CATALOG NUMBER: LD4D50D010-EU4DR4040509035-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 | 103 | 101 | 100 | 99 | 98 | 97 | 96 | | | | | | | | | | | | | | | | | | | |
| 2 | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 99 | 102 | 99 | 97 | 99 | 97 | 95 | 96 | 95 | 93 | 92 | | | | | | | | | | | | | | | | | | | |
| 3 | 106 | 101 | 97 | 94 | 104 | 100 | 96 | 93 | 97 | 94 | 92 | 95 | 93 | 90 | 93 | 91 | 89 | 88 | | | | | | | | | | | | | | | | | | | |
| 4 | 102 | 97 | 92 | 89 | 101 | 95 | 91 | 88 | 93 | 90 | 87 | 92 | 89 | 86 | 90 | 87 | 85 | 84 | | | | | | | | | | | | | | | | | | | |
| 5 | 99 | 92 | 88 | 84 | 97 | 91 | 87 | 84 | 90 | 86 | 83 | 88 | 85 | 83 | 87 | 84 | 82 | 81 | | | | | | | | | | | | | | | | | | | |
| 6 | 95 | 88 | 84 | 80 | 94 | 88 | 83 | 80 | 86 | 82 | 80 | 85 | 82 | 79 | 84 | 81 | 79 | 77 | | | | | | | | | | | | | | | | | | | |
| 7 | 92 | 85 | 80 | 77 | 91 | 84 | 80 | 77 | 83 | 79 | 76 | 82 | 79 | 76 | 81 | 78 | 76 | 74 | | | | | | | | | | | | | | | | | | | |
| 8 | 89 | 82 | 77 | 74 | 88 | 81 | 77 | 74 | 80 | 76 | 73 | 79 | 76 | 73 | 78 | 75 | 73 | 72 | | | | | | | | | | | | | | | | | | | |
| 9 | 86 | 79 | 74 | 71 | 85 | 78 | 74 | 71 | 77 | 73 | 71 | 76 | 73 | 70 | 76 | 72 | 70 | 69 | | | | | | | | | | | | | | | | | | | |
| 10 | 83 | 76 | 71 | 68 | 82 | 75 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 73 | 70 | 68 | 67 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1224485 |
| 5° | 1218535 |
| 10° | 1151789 |
| 15° | 979158 |
| 20° | 667371 |
| 25° | 278460 |
| 30° | 87557 |
| 35° | 40695 |
| 40° | 22507 |
| 45° | 10322 |
| 50° | 5014 |
| 55° | 2743 |
| 60° | 1420 |
| 65° | 517 |
| 70° | 224 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10322 cd/sqm



TEST NUMBER: P749280

CATALOG NUMBER: LD4D50D010-EU4DR4040509035-4LBCSSQMB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1037.4 | 21.6 |
| 10°-20° | 2324.1 | 48.3 |
| 20°-30° | 1163.4 | 24.2 |
| 30°-40° | 213.3 | 4.4 |
| 40°-50° | 58.9 | 1.2 |
| 50°-60° | 13.8 | 0.3 |
| 60°-70° | 2.6 | 0.1 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 4524.8 | 94.0 |
| 0°-40° | 4738.1 | 98.4 |
| 0°-60° | 4810.8 | 99.9 |
| 0°-90° | 4813.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 4813.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 11207 | |
| 5° | 11110 | ### |
| 15° | 8656 | 2324 |
| 25° | 2310 | 1163 |
| 35° | 305 | 213 |
| 45° | 67 | 59 |
| 55° | 14 | 14 |
| 65° | 2 | 3 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P749280
CATALOG NUMBER: LD4D50D010-EU4DR4040509035-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 11207.0 |
| 2.5° | 11190.7 |
| 5° | 11110.1 |
| 7.5° | 10853.5 |
| 10° | 10381.5 |
| 12.5° | 9645.6 |
| 15° | 8656.3 |
| 17.5° | 7369.9 |
| 20° | 5739.7 |
| 22.5° | 3913.1 |
| 25° | 2309.8 |
| 27.5° | 1221.0 |
| 30° | 694.0 |
| 32.5° | 448.5 |
| 35° | 305.1 |
| 37.5° | 218.0 |
| 40° | 157.8 |
| 42.5° | 108.0 |
| 45° | 66.8 |
| 47.5° | 42.6 |
| 50° | 29.5 |
| 52.5° | 21.0 |
| 55° | 14.4 |
| 57.5° | 9.2 |
| 60° | 6.5 |
| 62.5° | 3.9 |
| 65° | 2.0 |
| 67.5° | 1.3 |
| 70° | 0.7 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)