

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749616

Luminaire Tested: LD4D50D010-EU4DR6040509040-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P749616
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR6040509040-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4096.4 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P749616

CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P749616

CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	531564
5°	544640
10°	551214
15°	525103
20°	462987
25°	374471
30°	253298
35°	126927
40°	20596
45°	20149
50°	20551
55°	20859
60°	21437
65°	21924
70°	22458
75°	22712
80°	21896
85°	18303

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 22712 cd/sqm



TEST NUMBER: P749616

CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	474.6	11.6
10°-20°	1284.1	31.3
20°-30°	1381.6	33.7
30°-40°	600.5	14.7
40°-50°	100.9	2.5
50°-60°	98.0	2.4
60°-70°	83.9	2.0
70°-80°	56.1	1.4
80°-90°	16.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3140.2	76.7
0°-40°	3740.8	91.3
0°-60°	3939.7	96.2
0°-90°	4096.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4096.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4865	
5°	4966	475
15°	4642	1284
25°	3106	1382
35°	952	601
45°	130	101
55°	110	98
65°	85	84
75°	54	56
85°	15	17
90°	0	



TEST NUMBER: P749616

CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4865.1
2.5°	5001.8
5°	4965.8
7.5°	4977.2
10°	4968.3
12.5°	4865.7
15°	4642.2
17.5°	4342.1
20°	3981.9
22.5°	3596.3
25°	3106.2
27.5°	2484.5
30°	2007.7
32.5°	1547.4
35°	951.6
37.5°	407.1
40°	144.4
42.5°	133.0
45°	130.4
47.5°	126.0
50°	120.9
52.5°	115.2
55°	109.5
57.5°	103.8
60°	98.1
62.5°	91.8
65°	84.8
67.5°	77.9
70°	70.3
72.5°	62.0
75°	53.8
77.5°	44.3
80°	34.8
82.5°	24.7
85°	14.6
87.5°	5.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)