

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752011

Luminaire Tested: LD4D65D010-EU4DR6555659035-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P752011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR6555659035-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5917.2 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752011

CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P752011

CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93					93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85					85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78					78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72					72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66					66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61					61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56					56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52					52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49					49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46					46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	313786
5°	312998
10°	312732
15°	303089
20°	275924
25°	240451
30°	199990
35°	158460
40°	114369
45°	72255
50°	37662
55°	20019
60°	10513
65°	5777
70°	2425
75°	2663
80°	1850
85°	1608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 72255 cd/sqm



TEST NUMBER: P752011

CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	508.1	8.6
10°-20°	1391.3	23.5
20°-30°	1700.7	28.7
30°-40°	1379.9	23.3
40°-50°	687.6	11.6
50°-60°	191.8	3.2
60°-70°	43.6	0.7
70°-80°	11.3	0.2
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3600.1	60.8
0°-40°	4980.0	84.2
0°-60°	5859.5	99.0
0°-90°	5917.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5917.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5373	
5°	5339	508
15°	5013	1391
25°	3731	1701
35°	2222	1380
45°	875	688
55°	197	192
65°	42	44
75°	12	11
85°	2	3
90°	0	



TEST NUMBER: P752011

CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	5372.7
2.5°	5368.8
5°	5338.8
7.5°	5321.4
10°	5273.3
12.5°	5175.4
15°	5012.7
17.5°	4758.5
20°	4439.5
22.5°	4095.3
25°	3731.3
27.5°	3342.1
30°	2965.5
32.5°	2593.6
35°	2222.5
37.5°	1852.2
40°	1500.1
42.5°	1170.1
45°	874.8
47.5°	609.5
50°	414.5
52.5°	285.8
55°	196.6
57.5°	132.6
60°	90.0
62.5°	62.4
65°	41.8
67.5°	21.3
70°	14.2
72.5°	13.4
75°	11.8
77.5°	7.9
80°	5.5
82.5°	3.9
85°	2.4
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)