

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752025

Luminaire Tested: LD4D65D010-EU4DR6555659040-4LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P752025
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR6555659040-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6309.5 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752025
CATALOG NUMBER: LD4D65D010-EU4DR6555659040-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P752025

CATALOG NUMBER: LD4D65D010-EU4DR6555659040-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	334590
5°	333746
10°	333459
15°	323181
20°	294216
25°	256387
30°	213242
35°	168962
40°	121947
45°	77045
50°	40160
55°	21342
60°	11214
65°	6164
70°	2596
75°	2843
80°	1984
85°	1675

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 77045 cd/sqm



TEST NUMBER: P752025

CATALOG NUMBER: LD4D65D010-EU4DR6555659040-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	541.8	8.6
10°-20°	1483.6	23.5
20°-30°	1813.4	28.7
30°-40°	1471.3	23.3
40°-50°	733.2	11.6
50°-60°	204.5	3.2
60°-70°	46.5	0.7
70°-80°	12.1	0.2
80°-90°	3.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3838.8	60.8
0°-40°	5310.1	84.2
0°-60°	6247.8	99.0
0°-90°	6309.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6309.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5729	
5°	5693	542
15°	5345	1484
25°	3979	1813
35°	2370	1471
45°	933	733
55°	210	205
65°	45	46
75°	13	12
85°	2	3
90°	0	



TEST NUMBER: P752025

CATALOG NUMBER: LD4D65D010-EU4DR6555659040-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5728.9
2.5°	5724.7
5°	5692.7
7.5°	5674.2
10°	5622.8
12.5°	5518.4
15°	5345.0
17.5°	5073.9
20°	4733.8
22.5°	4366.7
25°	3978.6
27.5°	3563.6
30°	3162.0
32.5°	2765.5
35°	2369.8
37.5°	1975.0
40°	1599.5
42.5°	1247.6
45°	932.8
47.5°	649.9
50°	442.0
52.5°	304.8
55°	209.6
57.5°	141.4
60°	96.0
62.5°	66.5
65°	44.6
67.5°	22.7
70°	15.2
72.5°	14.3
75°	12.6
77.5°	8.4
80°	5.9
82.5°	4.2
85°	2.5
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)