

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750501

Luminaire Tested: LD4D55D010-EU4DR7055659024-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P750501  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D55D010-EU4DR7055659024-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3893.4 lumens  
Efficiency: N/A  
Efficacy: 66.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P750501

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P750501

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	478267
5°	464059
10°	451119
15°	445198
20°	415722
25°	312312
30°	220773
35°	78202
40°	41120
45°	43806
50°	45351
55°	46213
60°	46501
65°	45502
70°	42967
75°	39809
80°	35299
85°	28708

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 46507 cd/sqm



TEST NUMBER: P750501

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	399.1	10.3
10°-20°	1094.7	28.1
20°-30°	1205.6	31.0
30°-40°	460.6	11.8
40°-50°	217.5	5.6
50°-60°	216.2	5.6
60°-70°	173.1	4.4
70°-80°	99.5	2.6
80°-90°	27.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2699.3	69.3
0°-40°	3160.0	81.2
0°-60°	3593.7	92.3
0°-90°	3893.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3893.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4377	
5°	4231	399
15°	3936	1095
25°	2591	1206
35°	586	461
45°	284	217
55°	243	216
65°	176	173
75°	94	100
85°	23	27
90°	0	



TEST NUMBER: P750501

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4377.3
2.5°	4331.5
5°	4231.1
7.5°	4147.2
10°	4066.1
12.5°	3997.5
15°	3935.8
17.5°	3786.8
20°	3575.4
22.5°	3119.4
25°	2590.6
27.5°	2255.2
30°	1749.9
32.5°	1130.4
35°	586.3
37.5°	316.7
40°	288.3
42.5°	286.2
45°	283.5
47.5°	277.2
50°	266.8
52.5°	255.0
55°	242.6
57.5°	228.7
60°	212.8
62.5°	194.7
65°	176.0
67.5°	155.2
70°	134.5
72.5°	113.7
75°	94.3
77.5°	74.2
80°	56.1
82.5°	39.5
85°	22.9
87.5°	9.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)