

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749890

Luminaire Tested: LD4D55D010-EU4DR3055659027-4LBSQW1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P749890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR3055659027-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4360.4 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P749890

CATALOG NUMBER: LD4D55D010-EU4DR3055659027-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P749890

CATALOG NUMBER: LD4D55D010-EU4DR3055659027-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1073200	1073200	1073200
5°	1042393	1041171	1042446
10°	902868	896502	902650
15°	589073	585911	582963
20°	292923	303912	292524
25°	147554	166387	144530
30°	59076	64371	51475
35°	27397	26248	21996
40°	11831	13140	11141
45°	8346	10359	8422
50°	2870	7538	3037
55°	1655	3123	1748
60°	1163	1362	1163
65°	743	743	743
70°	470	313	470
75°	0	207	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 10359 cd/sqm



TEST NUMBER: P749890

CATALOG NUMBER: LD4D55D010-EU4DR3055659027-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1232.9	28.3
10°-20°	1985.6	45.5
20°-30°	858.0	19.7
30°-40°	195.6	4.5
40°-50°	67.2	1.5
50°-60°	16.4	0.4
60°-70°	4.3	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4076.6	93.5
0°-40°	4272.1	98.0
0°-60°	4355.7	99.9
0°-90°	4360.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4360.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	14021	14021	14021	14021	14021	
5°	13566	13553	13551	13579	13567	1234
15°	7434	7344	7394	7370	7357	1990
25°	1747	1813	1970	1767	1711	836
35°	293	299	281	279	235	199
45°	77	96	96	96	78	55
55°	12	13	23	14	13	12
65°	4	4	4	4	4	4
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P749890

CATALOG NUMBER: LD4D55D010-EU4DR3055659027-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	14020.8	14020.8	14020.8	14020.8	14020.8
2.5°	13927.9	13918.2	13923.7	13930.6	13933.4
5°	13566.5	13553.4	13550.6	13578.9	13567.2
7.5°	12837.5	12818.9	12790.7	12854.7	12914.6
10°	11616.3	11595.7	11534.4	11564.7	11613.5
12.5°	9813.5	9746.7	9745.3	9841.7	9828.6
15°	7433.7	7344.3	7393.8	7369.7	7356.6
17.5°	4999.0	4964.5	5030.6	5010.7	4924.6
20°	3596.1	3605.0	3731.0	3667.7	3591.2
22.5°	2624.1	2656.4	2805.8	2642.7	2582.8
25°	1747.1	1813.2	1970.1	1767.1	1711.3
27.5°	1074.6	1104.8	1263.9	1060.8	1030.5
30°	668.4	653.3	728.3	625.0	582.4
32.5°	438.5	419.2	443.3	397.9	363.5
35°	293.2	299.4	280.9	278.8	235.4
37.5°	183.1	210.6	185.9	198.3	151.4
40°	118.4	152.8	131.5	145.2	111.5
42.5°	97.1	117.7	108.1	115.0	99.1
45°	77.1	95.7	95.7	95.7	77.8
47.5°	42.7	64.0	81.9	65.4	45.4
50°	24.1	32.4	63.3	33.7	25.5
52.5°	16.5	18.6	43.4	19.3	17.2
55°	12.4	13.1	23.4	13.8	13.1
57.5°	9.6	10.3	12.4	10.3	9.6
60°	7.6	7.6	8.9	8.3	7.6
62.5°	5.5	5.5	6.2	5.5	5.5
65°	4.1	4.1	4.1	4.1	4.1
67.5°	2.1	2.8	2.8	2.8	2.8
70°	2.1	1.4	1.4	1.4	2.1
72.5°	1.4	0.7	0.7	0.7	0.7
75°	0.0	0.0	0.7	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)