

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751814

Luminaire Tested: LD4D65D010-EU4DR5055659050-4LBSQW1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR5055659050-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6804.4 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751814

CATALOG NUMBER: LD4D65D010-EU4DR5055659050-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P751814

CATALOG NUMBER: LD4D65D010-EU4DR5055659050-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95			95																
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			90																
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85			85																
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80			80																
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76			76																
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72			72																
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69			69																
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65			65																
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62			62																
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59			59																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1197891
5°	1185335
10°	1165812
15°	1061562
20°	883337
25°	627035
30°	331898
35°	135250
40°	50234
45°	22992
50°	9434
55°	4934
60°	2426
65°	724
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22992 cd/sqm



TEST NUMBER: P751814

CATALOG NUMBER: LD4D65D010-EU4DR5055659050-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1021.5	15.0
10°-20°	2581.6	37.9
20°-30°	2318.9	34.1
30°-40°	726.1	10.7
40°-50°	127.1	1.9
50°-60°	25.4	0.4
60°-70°	3.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5922.0	87.0
0°-40°	6648.1	97.7
0°-60°	6800.6	99.9
0°-90°	6804.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6804.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10964	
5°	10807	###
15°	9385	2582
25°	5201	2319
35°	1014	726
45°	149	127
55°	26	25
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751814

CATALOG NUMBER: LD4D65D010-EU4DR5055659050-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	10963.6
2.5°	10909.0
5°	10807.4
7.5°	10652.1
10°	10507.9
12.5°	10045.7
15°	9384.8
17.5°	8545.5
20°	7597.1
22.5°	6499.9
25°	5201.2
27.5°	3824.0
30°	2630.7
32.5°	1712.8
35°	1014.0
37.5°	582.3
40°	352.2
42.5°	229.2
45°	148.8
47.5°	90.6
50°	55.5
52.5°	37.9
55°	25.9
57.5°	17.6
60°	11.1
62.5°	6.5
65°	2.8
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)