

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750218

Luminaire Tested: LD4D55D010-EU4DR5055659035-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750218
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR5055659035-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5567.1 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P750218

CATALOG NUMBER: LD4D55D010-EU4DR5055659035-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P750218

CATALOG NUMBER: LD4D55D010-EU4DR5055659035-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100														
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95					95														
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90					90														
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85					85														
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80					80														
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76					76														
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72					72														
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69					69														
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65					65														
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62					62														
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59					59														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	980058
5°	969785
10°	953816
15°	868531
20°	722717
25°	513014
30°	271542
35°	110654
40°	41092
45°	18820
50°	7717
55°	4038
60°	1989
65°	595
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18820 cd/sqm



TEST NUMBER: P750218

CATALOG NUMBER: LD4D55D010-EU4DR5055659035-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	835.8	15.0
10°-20°	2112.2	37.9
20°-30°	1897.3	34.1
30°-40°	594.0	10.7
40°-50°	104.0	1.9
50°-60°	20.7	0.4
60°-70°	3.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4845.2	87.0
0°-40°	5439.2	97.7
0°-60°	5563.9	99.9
0°-90°	5567.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5567.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8970	
5°	8842	836
15°	7678	2112
25°	4255	1897
35°	830	594
45°	122	104
55°	21	21
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750218

CATALOG NUMBER: LD4D55D010-EU4DR5055659035-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8969.9
2.5°	8925.3
5°	8842.1
7.5°	8715.1
10°	8597.1
12.5°	8219.0
15°	7678.3
17.5°	6991.6
20°	6215.7
22.5°	5318.0
25°	4255.4
27.5°	3128.6
30°	2152.3
32.5°	1401.3
35°	829.6
37.5°	476.4
40°	288.1
42.5°	187.6
45°	121.8
47.5°	74.1
50°	45.4
52.5°	31.0
55°	21.2
57.5°	14.4
60°	9.1
62.5°	5.3
65°	2.3
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)