

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750383

Luminaire Tested: LD4D55D010-EU4DR6055659035-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR6055659035-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4424.6 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P750383

CATALOG NUMBER: LD4D55D010-EU4DR6055659035-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P750383

CATALOG NUMBER: LD4D55D010-EU4DR6055659035-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	574143
5°	588259
10°	595371
15°	567170
20°	500066
25°	404465
30°	273585
35°	137091
40°	22236
45°	21772
50°	22199
55°	22535
60°	23163
65°	23682
70°	24247
75°	24527
80°	23658
85°	19682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 24527 cd/sqm



TEST NUMBER: P750383

CATALOG NUMBER: LD4D55D010-EU4DR6055659035-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.6	11.6
10°-20°	1386.9	31.3
20°-30°	1492.2	33.7
30°-40°	648.6	14.7
40°-50°	108.9	2.5
50°-60°	105.9	2.4
60°-70°	90.6	2.0
70°-80°	60.6	1.4
80°-90°	18.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3391.7	76.7
0°-40°	4040.4	91.3
0°-60°	4255.3	96.2
0°-90°	4424.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4424.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5255	
5°	5364	513
15°	5014	1387
25°	3355	1492
35°	1028	649
45°	141	109
55°	118	106
65°	92	91
75°	58	61
85°	16	18
90°	0	



TEST NUMBER: P750383

CATALOG NUMBER: LD4D55D010-EU4DR6055659035-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5254.8
2.5°	5402.5
5°	5363.5
7.5°	5375.8
10°	5366.3
12.5°	5255.5
15°	5014.1
17.5°	4689.9
20°	4300.8
22.5°	3884.3
25°	3355.0
27.5°	2683.5
30°	2168.5
32.5°	1671.4
35°	1027.8
37.5°	439.7
40°	155.9
42.5°	143.6
45°	140.9
47.5°	136.1
50°	130.6
52.5°	124.5
55°	118.3
57.5°	112.2
60°	106.0
62.5°	99.2
65°	91.6
67.5°	84.1
70°	75.9
72.5°	67.0
75°	58.1
77.5°	47.9
80°	37.6
82.5°	26.7
85°	15.7
87.5°	5.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)