

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750461

Luminaire Tested: LD4D55D010-EU4DR6555659035-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750461
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR6555659035-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3707.4 lumens
Efficiency: N/A
Efficacy: 63.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P750461

CATALOG NUMBER: LD4D55D010-EU4DR6555659035-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P750461

CATALOG NUMBER: LD4D55D010-EU4DR6555659035-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	398835
5°	399163
10°	413219
15°	413899
20°	381061
25°	324681
30°	248555
35°	175598
40°	103649
45°	42075
50°	15247
55°	8496
60°	4873
65°	2689
70°	2811
75°	2195
80°	2265
85°	2006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 42075 cd/sqm



TEST NUMBER: P750461

CATALOG NUMBER: LD4D55D010-EU4DR6555659035-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	351.5	9.5
10°-20°	1013.9	27.3
20°-30°	1216.5	32.8
30°-40°	817.5	22.1
40°-50°	244.7	6.6
50°-60°	43.2	1.2
60°-70°	12.3	0.3
70°-80°	6.0	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2581.9	69.6
0°-40°	3399.4	91.7
0°-60°	3687.2	99.5
0°-90°	3707.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3707.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3650	
5°	3639	351
15°	3659	1014
25°	2693	1216
35°	1316	818
45°	272	245
55°	45	43
65°	10	12
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P750461

CATALOG NUMBER: LD4D55D010-EU4DR6555659035-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3650.3
2.5°	3665.8
5°	3639.4
7.5°	3694.4
10°	3724.5
12.5°	3717.2
15°	3659.1
17.5°	3517.0
20°	3277.3
22.5°	2995.1
25°	2693.2
27.5°	2352.4
30°	1970.1
32.5°	1623.6
35°	1316.5
37.5°	1013.1
40°	726.7
42.5°	474.6
45°	272.3
47.5°	144.2
50°	89.7
52.5°	62.2
55°	44.6
57.5°	32.2
60°	22.3
62.5°	14.5
65°	10.4
67.5°	9.3
70°	8.8
72.5°	6.7
75°	5.2
77.5°	4.7
80°	3.6
82.5°	2.6
85°	1.6
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)