

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752853

Luminaire Tested: LD4D70BD010-EU4DR7070959027-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752853
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR7070959027-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4105.2 lumens
Efficiency: N/A
Efficacy: 61.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752853
CATALOG NUMBER: LD4D70BD010-EU4DR7070959027-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P752853
 CATALOG NUMBER: LD4D70BD010-EU4DR7070959027-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	504282
5°	489296
10°	475660
15°	469416
20°	438337
25°	329298
30°	232784
35°	82457
40°	43359
45°	46185
50°	47815
55°	48727
60°	49014
65°	47984
70°	45299
75°	41962
80°	37249
85°	30212

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 49028 cd/sqm



TEST NUMBER: P752853

CATALOG NUMBER: LD4D70BD010-EU4DR7070959027-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	420.8	10.3
10°-20°	1154.2	28.1
20°-30°	1271.2	31.0
30°-40°	485.7	11.8
40°-50°	229.3	5.6
50°-60°	228.0	5.6
60°-70°	182.5	4.4
70°-80°	104.9	2.6
80°-90°	28.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2846.2	69.3
0°-40°	3331.9	81.2
0°-60°	3789.2	92.3
0°-90°	4105.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4105.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4615	
5°	4461	421
15°	4150	1154
25°	2732	1271
35°	618	486
45°	299	229
55°	256	228
65°	186	183
75°	99	105
85°	24	29
90°	0	



TEST NUMBER: P752853

CATALOG NUMBER: LD4D70BD010-EU4DR7070959027-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4615.4
2.5°	4567.2
5°	4461.2
7.5°	4372.8
10°	4287.3
12.5°	4215.0
15°	4149.9
17.5°	3992.8
20°	3769.9
22.5°	3289.1
25°	2731.5
27.5°	2377.9
30°	1845.1
32.5°	1191.9
35°	618.2
37.5°	334.0
40°	304.0
42.5°	301.8
45°	298.9
47.5°	292.3
50°	281.3
52.5°	268.9
55°	255.8
57.5°	241.1
60°	224.3
62.5°	205.3
65°	185.6
67.5°	163.7
70°	141.8
72.5°	119.8
75°	99.4
77.5°	78.2
80°	59.2
82.5°	41.7
85°	24.1
87.5°	9.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)