

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749919

Luminaire Tested: LD4D55D010-EU4DR3055659040-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P749919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR3055659040-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5162.0 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P749919

CATALOG NUMBER: LD4D55D010-EU4DR3055659040-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P749919

CATALOG NUMBER: LD4D55D010-EU4DR3055659040-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96								
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92								
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89								
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85								
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82								
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79								
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77								
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74								
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72								
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1270490	1270490	1270490
5°	1234013	1232577	1234075
10°	1068840	1061308	1068591
15°	697367	693619	690132
20°	346765	359782	346301
25°	174681	196977	171100
30°	69939	76205	60932
35°	32443	31070	26042
40°	14009	15548	13189
45°	9883	12265	9970
50°	3394	8931	3596
55°	1962	3697	2068
60°	1378	1623	1378
65°	887	887	887
70°	537	358	537
75°	0	237	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 12265 cd/sqm



TEST NUMBER: P749919

CATALOG NUMBER: LD4D55D010-EU4DR3055659040-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1459.6	28.3
10°-20°	2350.6	45.5
20°-30°	1015.8	19.7
30°-40°	231.5	4.5
40°-50°	79.5	1.5
50°-60°	19.4	0.4
60°-70°	5.0	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4826.0	93.5
0°-40°	5057.5	98.0
0°-60°	5156.4	99.9
0°-90°	5162.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5162.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	16598	16598	16598	16598	16598	
5°	16060	16045	16042	16075	16061	1461
15°	8800	8694	8753	8724	8709	2356
25°	2068	2146	2332	2092	2026	990
35°	347	354	332	330	279	235
45°	91	113	113	113	92	65
55°	15	16	28	16	16	14
65°	5	5	5	5	5	5
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P749919

CATALOG NUMBER: LD4D55D010-EU4DR3055659040-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	16598.3	16598.3	16598.3	16598.3	16598.3
2.5°	16488.2	16476.8	16483.4	16491.5	16494.8
5°	16060.4	16044.9	16041.7	16075.1	16061.2
7.5°	15197.4	15175.4	15142.0	15217.8	15288.7
10°	13751.7	13727.3	13654.8	13690.6	13748.5
12.5°	11617.5	11538.4	11536.8	11650.9	11635.4
15°	8800.3	8694.4	8753.0	8724.5	8709.0
17.5°	5917.9	5877.2	5955.4	5931.8	5829.9
20°	4257.1	4267.7	4416.9	4341.9	4251.4
22.5°	3106.5	3144.8	3321.6	3128.5	3057.6
25°	2068.3	2146.5	2332.3	2091.9	2025.9
27.5°	1272.1	1307.9	1496.2	1255.8	1219.9
30°	791.3	773.4	862.2	739.9	689.4
32.5°	519.1	496.3	524.8	471.0	430.3
35°	347.2	354.5	332.5	330.0	278.7
37.5°	216.8	249.4	220.0	234.7	179.3
40°	140.2	180.9	155.6	171.9	132.0
42.5°	114.9	139.4	127.9	136.1	117.3
45°	91.3	113.3	113.3	113.3	92.1
47.5°	50.5	75.8	97.0	77.4	53.8
50°	28.5	38.3	75.0	39.9	30.2
52.5°	19.6	22.0	51.3	22.8	20.4
55°	14.7	15.5	27.7	16.3	15.5
57.5°	11.4	12.2	14.7	12.2	11.4
60°	9.0	9.0	10.6	9.8	9.0
62.5°	6.5	6.5	7.3	6.5	6.5
65°	4.9	4.9	4.9	4.9	4.9
67.5°	2.4	3.3	3.3	3.3	3.3
70°	2.4	1.6	1.6	1.6	2.4
72.5°	1.6	0.8	0.8	0.8	0.8
75°	0.0	0.0	0.8	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)