

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752779

Luminaire Tested: LD4D70BD010-EU4DR6570959030-4LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P752779
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6570959030-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6080.2 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752779

CATALOG NUMBER: LD4D70BD010-EU4DR6570959030-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P752779

CATALOG NUMBER: LD4D70BD010-EU4DR6570959030-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	322424
5°	321610
10°	321337
15°	311433
20°	283519
25°	247069
30°	205493
35°	162823
40°	117518
45°	74245
50°	38697
55°	20568
60°	10805
65°	5942
70°	2493
75°	2753
80°	1917
85°	1608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 74245 cd/sqm



TEST NUMBER: P752779

CATALOG NUMBER: LD4D70BD010-EU4DR6570959030-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	522.1	8.6
10°-20°	1429.6	23.5
20°-30°	1747.5	28.7
30°-40°	1417.9	23.3
40°-50°	706.6	11.6
50°-60°	197.1	3.2
60°-70°	44.8	0.7
70°-80°	11.7	0.2
80°-90°	3.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3699.2	60.8
0°-40°	5117.1	84.2
0°-60°	6020.8	99.0
0°-90°	6080.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6080.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5521	
5°	5486	522
15°	5151	1430
25°	3834	1748
35°	2284	1418
45°	899	707
55°	202	197
65°	43	45
75°	12	12
85°	2	3
90°	0	



TEST NUMBER: P752779

CATALOG NUMBER: LD4D70BD010-EU4DR6570959030-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5520.6
2.5°	5516.6
5°	5485.7
7.5°	5467.9
10°	5418.4
12.5°	5317.8
15°	5150.7
17.5°	4889.4
20°	4561.7
22.5°	4208.0
25°	3834.0
27.5°	3434.1
30°	3047.1
32.5°	2665.0
35°	2283.7
37.5°	1903.2
40°	1541.4
42.5°	1202.3
45°	898.9
47.5°	626.3
50°	425.9
52.5°	293.7
55°	202.0
57.5°	136.3
60°	92.5
62.5°	64.1
65°	43.0
67.5°	21.9
70°	14.6
72.5°	13.8
75°	12.2
77.5°	8.1
80°	5.7
82.5°	4.1
85°	2.4
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)