

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752867

Luminaire Tested: LD4D70BD010-EU4DR7070959030-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR7070959030-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5632.7 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752867
CATALOG NUMBER: LD4D70BD010-EU4DR7070959030-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752867

CATALOG NUMBER: LD4D70BD010-EU4DR7070959030-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65		
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	691916
5°	671362
10°	652641
15°	644077
20°	601445
25°	451831
30°	319408
35°	113135
40°	59491
45°	63368
50°	65612
55°	66843
60°	67261
65°	65848
70°	62134
75°	57581
80°	51092
85°	41495

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 67289 cd/sqm



TEST NUMBER: P752867

CATALOG NUMBER: LD4D70BD010-EU4DR7070959030-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	577.4	10.3
10°-20°	1583.7	28.1
20°-30°	1744.2	31.0
30°-40°	666.4	11.8
40°-50°	314.7	5.6
50°-60°	312.8	5.6
60°-70°	250.5	4.4
70°-80°	144.0	2.6
80°-90°	39.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3905.2	69.3
0°-40°	4571.6	81.2
0°-60°	5199.1	92.3
0°-90°	5632.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5632.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6333	
5°	6121	577
15°	5694	1584
25°	3748	1744
35°	848	666
45°	410	315
55°	351	313
65°	255	250
75°	136	144
85°	33	39
90°	0	



TEST NUMBER: P752867

CATALOG NUMBER: LD4D70BD010-EU4DR7070959030-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6332.7
2.5°	6266.6
5°	6121.2
7.5°	5999.9
10°	5882.5
12.5°	5783.3
15°	5694.0
17.5°	5478.5
20°	5172.7
22.5°	4512.9
25°	3747.9
27.5°	3262.6
30°	2531.7
32.5°	1635.3
35°	848.2
37.5°	458.2
40°	417.1
42.5°	414.1
45°	410.1
47.5°	401.1
50°	386.0
52.5°	369.0
55°	350.9
57.5°	330.9
60°	307.8
62.5°	281.7
65°	254.7
67.5°	224.6
70°	194.5
72.5°	164.4
75°	136.4
77.5°	107.3
80°	81.2
82.5°	57.2
85°	33.1
87.5°	13.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)