

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752724

Luminaire Tested: LD4D70BD010-EU4DR6070959035-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6070959035-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6178.8 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752724
CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752724

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	801766
5°	821489
10°	831409
15°	792032
20°	698323
25°	564829
30°	382061
35°	191444
40°	31051
45°	30394
50°	31004
55°	31469
60°	32341
65°	33092
70°	33862
75°	34279
80°	33033
85°	27580

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 34279 cd/sqm



TEST NUMBER: P752724

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	715.9	11.6
10°-20°	1936.8	31.3
20°-30°	2083.8	33.7
30°-40°	905.8	14.7
40°-50°	152.1	2.5
50°-60°	147.9	2.4
60°-70°	126.5	2.0
70°-80°	84.7	1.4
80°-90°	25.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4736.5	76.7
0°-40°	5642.3	91.3
0°-60°	5942.3	96.2
0°-90°	6178.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6178.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7338	
5°	7490	716
15°	7002	1937
25°	4685	2084
35°	1435	906
45°	197	152
55°	165	148
65°	128	127
75°	81	85
85°	22	25
90°	0	



TEST NUMBER: P752724

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7338.1
2.5°	7544.4
5°	7490.0
7.5°	7507.2
10°	7493.8
12.5°	7339.1
15°	7002.0
17.5°	6549.3
20°	6005.9
22.5°	5424.3
25°	4685.2
27.5°	3747.4
30°	3028.3
32.5°	2334.0
35°	1435.3
37.5°	614.1
40°	217.7
42.5°	200.5
45°	196.7
47.5°	190.0
50°	182.4
52.5°	173.8
55°	165.2
57.5°	156.6
60°	148.0
62.5°	138.5
65°	128.0
67.5°	117.5
70°	106.0
72.5°	93.6
75°	81.2
77.5°	66.8
80°	52.5
82.5°	37.2
85°	22.0
87.5°	7.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)