

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750552

Luminaire Tested: LD4D55D010-EU4DR7055659040-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR7055659040-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3608.7 lumens
Efficiency: N/A
Efficacy: 62.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P750552

CATALOG NUMBER: LD4D55D010-EU4DR7055659040-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P750552

CATALOG NUMBER: LD4D55D010-EU4DR7055659040-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	443293
5°	430114
10°	418134
15°	412644
20°	385328
25°	289479
30°	204637
35°	72480
40°	38111
45°	40592
50°	42036
55°	42822
60°	43092
65°	42193
70°	39804
75°	36896
80°	32719
85°	26577

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 43111 cd/sqm



TEST NUMBER: P750552

CATALOG NUMBER: LD4D55D010-EU4DR7055659040-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.9	10.3
10°-20°	1014.6	28.1
20°-30°	1117.5	31.0
30°-40°	426.9	11.8
40°-50°	201.6	5.6
50°-60°	200.4	5.6
60°-70°	160.5	4.4
70°-80°	92.2	2.6
80°-90°	25.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2502.0	69.3
0°-40°	2928.9	81.2
0°-60°	3330.9	92.3
0°-90°	3608.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3608.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4057	
5°	3922	370
15°	3648	1015
25°	2401	1117
35°	543	427
45°	263	202
55°	225	200
65°	163	160
75°	87	92
85°	21	25
90°	0	



TEST NUMBER: P750552

CATALOG NUMBER: LD4D55D010-EU4DR7055659040-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4057.2
2.5°	4014.8
5°	3921.6
7.5°	3843.9
10°	3768.8
12.5°	3705.2
15°	3648.0
17.5°	3509.9
20°	3314.0
22.5°	2891.3
25°	2401.2
27.5°	2090.3
30°	1622.0
32.5°	1047.7
35°	543.4
37.5°	293.6
40°	267.2
42.5°	265.3
45°	262.7
47.5°	256.9
50°	247.3
52.5°	236.4
55°	224.8
57.5°	212.0
60°	197.2
62.5°	180.5
65°	163.2
67.5°	143.9
70°	124.6
72.5°	105.3
75°	87.4
77.5°	68.7
80°	52.0
82.5°	36.6
85°	21.2
87.5°	8.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)