

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752892

Luminaire Tested: LD4D70BD010-EU4DR7070959040-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR7070959040-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4473.7 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752892
CATALOG NUMBER: LD4D70BD010-EU4DR7070959040-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P752892
 CATALOG NUMBER: LD4D70BD010-EU4DR7070959040-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	549538
5°	533211
10°	518352
15°	511552
20°	477684
25°	358859
30°	253677
35°	89860
40°	47253
45°	50327
50°	52116
55°	53090
60°	53429
65°	52301
70°	49356
75°	45719
80°	40584
85°	32970

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 53441 cd/sqm



TEST NUMBER: P752892

CATALOG NUMBER: LD4D70BD010-EU4DR7070959040-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	458.6	10.3
10°-20°	1257.8	28.1
20°-30°	1385.3	31.0
30°-40°	529.3	11.8
40°-50°	249.9	5.6
50°-60°	248.4	5.6
60°-70°	198.9	4.4
70°-80°	114.3	2.6
80°-90°	31.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3101.6	69.3
0°-40°	3630.9	81.2
0°-60°	4129.3	92.3
0°-90°	4473.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4473.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5030	
5°	4862	459
15°	4522	1258
25°	2977	1385
35°	674	529
45°	326	250
55°	279	248
65°	202	199
75°	108	114
85°	26	31
90°	0	



TEST NUMBER: P752892

CATALOG NUMBER: LD4D70BD010-EU4DR7070959040-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5029.6
2.5°	4977.1
5°	4861.6
7.5°	4765.2
10°	4672.1
12.5°	4593.2
15°	4522.4
17.5°	4351.2
20°	4108.3
22.5°	3584.3
25°	2976.7
27.5°	2591.3
30°	2010.7
32.5°	1298.8
35°	673.7
37.5°	363.9
40°	331.3
42.5°	328.9
45°	325.7
47.5°	318.5
50°	306.6
52.5°	293.0
55°	278.7
57.5°	262.8
60°	244.5
62.5°	223.8
65°	202.3
67.5°	178.4
70°	154.5
72.5°	130.6
75°	108.3
77.5°	85.2
80°	64.5
82.5°	45.4
85°	26.3
87.5°	10.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)