

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752749

Luminaire Tested: LD4D70BD010-EU4DR6070959050-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752749
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6070959050-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5782.6 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752749

CATALOG NUMBER: LD4D70BD010-EU4DR6070959050-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P752749

CATALOG NUMBER: LD4D70BD010-EU4DR6070959050-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	750348
5°	768811
10°	778088
15°	741232
20°	653547
25°	528601
30°	357560
35°	179173
40°	29068
45°	28447
50°	29016
55°	29450
60°	30265
65°	30972
70°	31690
75°	32083
80°	30957
85°	25825

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 32083 cd/sqm



TEST NUMBER: P752749

CATALOG NUMBER: LD4D70BD010-EU4DR6070959050-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	669.9	11.6
10°-20°	1812.6	31.3
20°-30°	1950.2	33.7
30°-40°	847.7	14.7
40°-50°	142.4	2.5
50°-60°	138.4	2.4
60°-70°	118.4	2.0
70°-80°	79.3	1.4
80°-90°	23.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4432.7	76.7
0°-40°	5280.4	91.3
0°-60°	5561.3	96.2
0°-90°	5782.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5782.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6868	
5°	7010	670
15°	6553	1813
25°	4385	1950
35°	1343	848
45°	184	142
55°	155	138
65°	120	118
75°	76	79
85°	21	24
90°	0	



TEST NUMBER: P752749

CATALOG NUMBER: LD4D70BD010-EU4DR6070959050-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6867.5
2.5°	7060.6
5°	7009.7
7.5°	7025.7
10°	7013.2
12.5°	6868.4
15°	6552.9
17.5°	6129.3
20°	5620.8
22.5°	5076.5
25°	4384.7
27.5°	3507.1
30°	2834.1
32.5°	2184.3
35°	1343.3
37.5°	574.7
40°	203.8
42.5°	187.7
45°	184.1
47.5°	177.9
50°	170.7
52.5°	162.7
55°	154.6
57.5°	146.6
60°	138.5
62.5°	129.6
65°	119.8
67.5°	109.9
70°	99.2
72.5°	87.6
75°	76.0
77.5°	62.6
80°	49.2
82.5°	34.9
85°	20.6
87.5°	7.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)