

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753542

Luminaire Tested: LD4D75BD010-EU4DR6570959024-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P753542  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D75BD010-EU4DR6570959024-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4119.2 lumens  
Efficiency: N/A  
Efficacy: 56.9 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P753542  
CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P753542

CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	443118
5°	443483
10°	459096
15°	459858
20°	423373
25°	360739
30°	276159
35°	195099
40°	115159
45°	46757
50°	16947
55°	9448
60°	5419
65°	2973
70°	3131
75°	2448
80°	2517
85°	2131

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 46757 cd/sqm



TEST NUMBER: P753542

CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	390.5	9.5
10°-20°	1126.5	27.3
20°-30°	1351.6	32.8
30°-40°	908.3	22.1
40°-50°	271.9	6.6
50°-60°	48.0	1.2
60°-70°	13.6	0.3
70°-80°	6.7	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2868.6	69.6
0°-40°	3776.8	91.7
0°-60°	4096.7	99.5
0°-90°	4119.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4119.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4056	
5°	4044	391
15°	4065	1126
25°	2992	1352
35°	1463	908
45°	303	272
55°	50	48
65°	12	14
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P753542  
CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4055.6
2.5°	4072.9
5°	4043.5
7.5°	4104.6
10°	4138.0
12.5°	4130.0
15°	4065.4
17.5°	3907.5
20°	3641.2
22.5°	3327.7
25°	2992.3
27.5°	2613.7
30°	2188.9
32.5°	1803.9
35°	1462.7
37.5°	1125.6
40°	807.4
42.5°	527.3
45°	302.6
47.5°	160.2
50°	99.7
52.5°	69.2
55°	49.6
57.5°	35.7
60°	24.8
62.5°	16.1
65°	11.5
67.5°	10.4
70°	9.8
72.5°	7.5
75°	5.8
77.5°	5.2
80°	4.0
82.5°	2.9
85°	1.7
87.5°	1.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)