

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751137

Luminaire Tested: LD4D60D010-EU4DR6055659027-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6055659027-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4673.6 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751137

CATALOG NUMBER: LD4D60D010-EU4DR6055659027-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P751137

CATALOG NUMBER: LD4D60D010-EU4DR6055659027-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	606441
5°	621359
10°	628866
15°	599080
20°	528204
25°	427226
30°	288977
35°	144814
40°	23491
45°	22992
50°	23457
55°	23811
60°	24474
65°	25026
70°	25620
75°	25920
80°	24980
85°	20810

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 25920 cd/sqm



TEST NUMBER: P751137

CATALOG NUMBER: LD4D60D010-EU4DR6055659027-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	541.5	11.6
10°-20°	1465.0	31.3
20°-30°	1576.2	33.7
30°-40°	685.1	14.7
40°-50°	115.1	2.5
50°-60°	111.9	2.4
60°-70°	95.7	2.0
70°-80°	64.0	1.4
80°-90°	19.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3582.6	76.7
0°-40°	4267.7	91.3
0°-60°	4494.7	96.2
0°-90°	4673.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4673.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5550	
5°	5665	541
15°	5296	1465
25°	3544	1576
35°	1086	685
45°	149	115
55°	125	112
65°	97	96
75°	61	64
85°	17	19
90°	0	



TEST NUMBER: P751137

CATALOG NUMBER: LD4D60D010-EU4DR6055659027-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5550.4
2.5°	5706.5
5°	5665.3
7.5°	5678.3
10°	5668.2
12.5°	5551.2
15°	5296.2
17.5°	4953.8
20°	4542.8
22.5°	4102.9
25°	3543.8
27.5°	2834.4
30°	2290.5
32.5°	1765.4
35°	1085.7
37.5°	464.5
40°	164.7
42.5°	151.7
45°	148.8
47.5°	143.7
50°	138.0
52.5°	131.5
55°	125.0
57.5°	118.5
60°	112.0
62.5°	104.7
65°	96.8
67.5°	88.8
70°	80.2
72.5°	70.8
75°	61.4
77.5°	50.6
80°	39.7
82.5°	28.2
85°	16.6
87.5°	5.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)