

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750985

Luminaire Tested: LD4D60D010-EU4DR5055659030-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR5055659030-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6057.9 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P750985
CATALOG NUMBER: LD4D60D010-EU4DR5055659030-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P750985

CATALOG NUMBER: LD4D60D010-EU4DR5055659030-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95																											
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																											
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85																											
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80																											
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76																											
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72																											
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69																											
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65																											
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62																											
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1066483
5°	1055301
10°	1037925
15°	945110
20°	786435
25°	558258
30°	295487
35°	120418
40°	44714
45°	20474
50°	8397
55°	4381
60°	2163
65°	646
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20474 cd/sqm



TEST NUMBER: P750985

CATALOG NUMBER: LD4D60D010-EU4DR5055659030-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	909.5	15.0
10°-20°	2298.4	37.9
20°-30°	2064.6	34.1
30°-40°	646.4	10.7
40°-50°	113.2	1.9
50°-60°	22.5	0.4
60°-70°	3.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5272.4	87.0
0°-40°	5918.8	97.7
0°-60°	6054.5	99.9
0°-90°	6057.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6057.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9761	
5°	9622	909
15°	8355	2298
25°	4631	2065
35°	903	646
45°	132	113
55°	23	23
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750985
CATALOG NUMBER: LD4D60D010-EU4DR5055659030-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	9760.9
2.5°	9712.3
5°	9621.8
7.5°	9483.6
10°	9355.2
12.5°	8943.7
15°	8355.3
17.5°	7608.1
20°	6763.7
22.5°	5786.9
25°	4630.7
27.5°	3404.5
30°	2342.1
32.5°	1524.9
35°	902.8
37.5°	518.5
40°	313.5
42.5°	204.1
45°	132.5
47.5°	80.6
50°	49.4
52.5°	33.7
55°	23.0
57.5°	15.6
60°	9.9
62.5°	5.8
65°	2.5
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)