

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753232

Luminaire Tested: LD4D75BD010-EU4DR4570959027-4LBCSSQMB

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P753232  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D75BD010-EU4DR4570959027-4LBCSSQMB  
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 45° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6834.7 lumens  
Efficiency: N/A  
Efficacy: 94.4 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P753232

CATALOG NUMBER: LD4D75BD010-EU4DR4570959027-4LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P753232  
 CATALOG NUMBER: LD4D75BD010-EU4DR4570959027-4LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95				
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90				
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85				
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81				
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77				
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73				
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69				
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66				
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63				
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1319903
5°	1282324
10°	1226844
15°	1122814
20°	890778
25°	556124
30°	306527
35°	137638
40°	54214
45°	25542
50°	12120
55°	6343
60°	3125
65°	750
70°	319
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25542 cd/sqm



TEST NUMBER: P753232

CATALOG NUMBER: LD4D75BD010-EU4DR4570959027-4LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1098.5	16.1
10°-20°	2703.7	39.6
20°-30°	2141.0	31.3
30°-40°	713.0	10.4
40°-50°	141.5	2.1
50°-60°	32.2	0.5
60°-70°	4.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5943.2	87.0
0°-40°	6656.2	97.4
0°-60°	6829.9	99.9
0°-90°	6834.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6834.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12080	
5°	11692	###
15°	9926	2704
25°	4613	2141
35°	1032	713
45°	165	142
55°	33	32
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753232

CATALOG NUMBER: LD4D75BD010-EU4DR4570959027-4LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	12080.3
2.5°	12001.5
5°	11691.7
7.5°	11436.1
10°	11058.0
12.5°	10554.4
15°	9926.3
17.5°	8981.9
20°	7661.1
22.5°	6087.7
25°	4613.0
27.5°	3377.8
30°	2429.6
32.5°	1652.3
35°	1031.9
37.5°	611.9
40°	380.1
42.5°	249.9
45°	165.3
47.5°	106.4
50°	71.3
52.5°	47.5
55°	33.3
57.5°	21.9
60°	14.3
62.5°	7.6
65°	2.9
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)