

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753582

Luminaire Tested: LD4D75BD010-EU4DR6570959035-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P753582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6570959035-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5711.0 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P753582
CATALOG NUMBER: LD4D75BD010-EU4DR6570959035-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P753582

CATALOG NUMBER: LD4D75BD010-EU4DR6570959035-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	614351
5°	614866
10°	636510
15°	637562
20°	586980
25°	500138
30°	382881
35°	270500
40°	159674
45°	64820
50°	23491
55°	13087
60°	7517
65°	4137
70°	4345
75°	3377
80°	3524
85°	3009

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 64820 cd/sqm



TEST NUMBER: P753582

CATALOG NUMBER: LD4D75BD010-EU4DR6570959035-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	541.4	9.5
10°-20°	1561.8	27.3
20°-30°	1873.8	32.8
30°-40°	1259.3	22.1
40°-50°	377.0	6.6
50°-60°	66.5	1.2
60°-70°	18.9	0.3
70°-80°	9.3	0.2
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3977.1	69.6
0°-40°	5236.3	91.7
0°-60°	5679.8	99.5
0°-90°	5711.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5711.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5623	
5°	5606	541
15°	5636	1562
25°	4149	1874
35°	2028	1259
45°	420	377
55°	69	67
65°	16	19
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P753582

CATALOG NUMBER: LD4D75BD010-EU4DR6570959035-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5622.8
2.5°	5646.8
5°	5606.1
7.5°	5690.8
10°	5737.1
12.5°	5725.9
15°	5636.4
17.5°	5417.5
20°	5048.3
22.5°	4613.7
25°	4148.6
27.5°	3623.6
30°	3034.8
32.5°	2501.0
35°	2028.0
37.5°	1560.5
40°	1119.5
42.5°	731.1
45°	419.5
47.5°	222.1
50°	138.2
52.5°	95.9
55°	68.7
57.5°	49.5
60°	34.4
62.5°	22.4
65°	16.0
67.5°	14.4
70°	13.6
72.5°	10.4
75°	8.0
77.5°	7.2
80°	5.6
82.5°	4.0
85°	2.4
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)