

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750711

Luminaire Tested: LD4D60D010-EU4DR3055659050-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3055659050-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5715.9 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P750711

CATALOG NUMBER: LD4D60D010-EU4DR3055659050-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P750711

CATALOG NUMBER: LD4D60D010-EU4DR3055659050-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96								
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92								
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89								
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85								
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82								
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79								
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77								
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74								
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72								
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1406837	1406837	1406837
5°	1366447	1364857	1366517
10°	1183553	1175205	1183273
15°	772213	768060	764201
20°	383983	398392	383469
25°	193422	218117	189461
30°	77443	84381	67473
35°	35919	34405	28836
40°	15508	17226	14608
45°	10944	13574	11041
50°	3763	9884	3977
55°	2162	4097	2282
60°	1516	1791	1516
65°	978	978	978
70°	604	403	604
75°	0	266	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 13574 cd/sqm



TEST NUMBER: P750711

CATALOG NUMBER: LD4D60D010-EU4DR3055659050-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1616.2	28.3
10°-20°	2602.9	45.5
20°-30°	1124.8	19.7
30°-40°	256.4	4.5
40°-50°	88.0	1.5
50°-60°	21.5	0.4
60°-70°	5.6	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5343.9	93.5
0°-40°	5600.3	98.0
0°-60°	5709.8	99.9
0°-90°	5715.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5715.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	18380	18380	18380	18380	18380	
5°	17784	17767	17763	17800	17785	1618
15°	9745	9628	9692	9661	9644	2609
25°	2290	2377	2583	2316	2243	1096
35°	384	392	368	366	309	261
45°	101	125	125	125	102	72
55°	16	17	31	18	17	16
65°	5	5	5	5	5	5
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P750711

CATALOG NUMBER: LD4D60D010-EU4DR3055659050-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	18379.6	18379.6	18379.6	18379.6	18379.6
2.5°	18257.8	18245.2	18252.4	18261.4	18265.0
5°	17784.0	17766.9	17763.3	17800.3	17784.9
7.5°	16828.4	16804.1	16767.1	16851.0	16929.5
10°	15227.6	15200.5	15120.2	15159.9	15224.0
12.5°	12864.3	12776.8	12774.9	12901.3	12884.1
15°	9744.8	9627.5	9692.4	9660.8	9643.7
17.5°	6553.1	6507.9	6594.6	6568.4	6455.6
20°	4714.0	4725.7	4890.9	4807.9	4707.7
22.5°	3439.9	3482.3	3678.1	3464.2	3385.7
25°	2290.2	2376.9	2582.6	2316.4	2243.3
27.5°	1408.6	1448.3	1656.8	1390.6	1350.9
30°	876.2	856.4	954.7	819.4	763.4
32.5°	574.8	549.5	581.1	521.6	476.5
35°	384.4	392.5	368.2	365.5	308.6
37.5°	240.0	276.1	243.6	259.9	198.5
40°	155.2	200.3	172.4	190.4	146.2
42.5°	127.2	154.3	141.7	150.7	129.9
45°	101.1	125.4	125.4	125.4	102.0
47.5°	55.9	83.9	107.4	85.7	59.6
50°	31.6	42.4	83.0	44.2	33.4
52.5°	21.7	24.4	56.8	25.3	22.6
55°	16.2	17.1	30.7	18.0	17.1
57.5°	12.6	13.5	16.2	13.5	12.6
60°	9.9	9.9	11.7	10.8	9.9
62.5°	7.2	7.2	8.1	7.2	7.2
65°	5.4	5.4	5.4	5.4	5.4
67.5°	2.7	3.6	3.6	3.6	3.6
70°	2.7	1.8	1.8	1.8	2.7
72.5°	1.8	0.9	0.9	0.9	0.9
75°	0.0	0.0	0.9	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)