

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753530

Luminaire Tested: LD4D75BD010-EU4DR6070959050-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P753530
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6070959050-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6884.7 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P753530
CATALOG NUMBER: LD4D75BD010-EU4DR6070959050-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P753530

CATALOG NUMBER: LD4D75BD010-EU4DR6070959050-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	893371
5°	915341
10°	926401
15°	882512
20°	778110
25°	629350
30°	425701
35°	213319
40°	34602
45°	33870
50°	34540
55°	35069
60°	36034
65°	36867
70°	37728
75°	38162
80°	36809
85°	30714

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 38162 cd/sqm



TEST NUMBER: P753530

CATALOG NUMBER: LD4D75BD010-EU4DR6070959050-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	797.6	11.6
10°-20°	2158.1	31.3
20°-30°	2321.9	33.7
30°-40°	1009.3	14.7
40°-50°	169.5	2.5
50°-60°	164.8	2.4
60°-70°	141.0	2.0
70°-80°	94.3	1.4
80°-90°	28.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5277.6	76.7
0°-40°	6286.9	91.3
0°-60°	6621.2	96.2
0°-90°	6884.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6884.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8176	
5°	8346	798
15°	7802	2158
25°	5220	2322
35°	1599	1009
45°	219	170
55°	184	165
65°	143	141
75°	90	94
85°	24	28
90°	0	



TEST NUMBER: P753530

CATALOG NUMBER: LD4D75BD010-EU4DR6070959050-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8176.5
2.5°	8406.3
5°	8345.7
7.5°	8364.8
10°	8350.0
12.5°	8177.6
15°	7801.9
17.5°	7297.6
20°	6692.1
22.5°	6044.1
25°	5220.4
27.5°	4175.5
30°	3374.2
32.5°	2600.6
35°	1599.3
37.5°	684.2
40°	242.6
42.5°	223.5
45°	219.2
47.5°	211.8
50°	203.2
52.5°	193.7
55°	184.1
57.5°	174.5
60°	164.9
62.5°	154.3
65°	142.6
67.5°	130.9
70°	118.1
72.5°	104.3
75°	90.4
77.5°	74.5
80°	58.5
82.5°	41.5
85°	24.5
87.5°	8.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)