

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752074

Luminaire Tested: LD4D65D010-EU4DR7055659027-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR7055659027-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5363.8 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752074

CATALOG NUMBER: LD4D65D010-EU4DR7055659027-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752074

CATALOG NUMBER: LD4D65D010-EU4DR7055659027-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	658897
5°	639314
10°	621499
15°	613344
20°	572737
25°	430264
30°	304155
35°	107747
40°	56653
45°	60339
50°	62484
55°	63662
60°	64049
65°	62694
70°	59163
75°	54837
80°	48638
85°	39489

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 64076 cd/sqm



TEST NUMBER: P752074

CATALOG NUMBER: LD4D65D010-EU4DR7055659027-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	549.8	10.3
10°-20°	1508.1	28.1
20°-30°	1660.9	31.0
30°-40°	634.6	11.8
40°-50°	299.6	5.6
50°-60°	297.9	5.6
60°-70°	238.5	4.4
70°-80°	137.1	2.6
80°-90°	37.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3718.8	69.3
0°-40°	4353.4	81.2
0°-60°	4951.0	92.3
0°-90°	5363.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5363.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6030	
5°	5829	550
15°	5422	1508
25°	3569	1661
35°	808	635
45°	390	300
55°	334	298
65°	242	239
75°	130	137
85°	32	37
90°	0	



TEST NUMBER: P752074

CATALOG NUMBER: LD4D65D010-EU4DR7055659027-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6030.5
2.5°	5967.4
5°	5829.0
7.5°	5713.5
10°	5601.8
12.5°	5507.2
15°	5422.3
17.5°	5217.0
20°	4925.8
22.5°	4297.5
25°	3569.0
27.5°	3106.9
30°	2410.8
32.5°	1557.3
35°	807.8
37.5°	436.3
40°	397.2
42.5°	394.3
45°	390.5
47.5°	381.9
50°	367.6
52.5°	351.4
55°	334.2
57.5°	315.1
60°	293.1
62.5°	268.3
65°	242.5
67.5°	213.9
70°	185.2
72.5°	156.6
75°	129.9
77.5°	102.2
80°	77.3
82.5°	54.4
85°	31.5
87.5°	12.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)