

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740953

Luminaire Tested: LD4D08D010-EU4DR200210IC9030-4LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P740953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR200210IC9030-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 740.3 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740953

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9030-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P740953

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9030-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	98	96	95	94															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	95	93	92	91															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	93	91	89	88															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	91	88	86	85															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	88	86	84	83															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	86	84	82	81															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	84	82	80	79															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	82	80	78	77															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	81	78	76	75															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	460403
5°	415373
10°	233131
15°	118499
20°	50172
25°	23159
30°	12263
35°	6602
40°	3537
45°	2086
50°	1207
55°	648
60°	415
65°	284
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2086 cd/sqm



TEST NUMBER: P740953

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9030-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.0	40.5
10°-20°	295.4	39.9
20°-30°	96.5	13.0
30°-40°	32.9	4.4
40°-50°	11.0	1.5
50°-60°	3.3	0.4
60°-70°	1.1	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	691.9	93.5
0°-40°	724.8	97.9
0°-60°	739.2	99.8
0°-90°	740.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	740.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4214	
5°	3787	300
15°	1048	295
25°	192	97
35°	50	33
45°	14	11
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P740953

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9030-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	4213.8
0.5°	4213.8
1°	4208.6
1.5°	4198.0
2°	4178.9
2.5°	4153.4
3°	4117.4
3.5°	4067.1
4°	3992.4
4.5°	3901.6
5°	3787.2
5.5°	3636.7
6°	3482.5
6.5°	3305.8
7°	3132.8
7.5°	2930.2
8°	2749.3
8.5°	2567.3
9°	2399.2
9.5°	2245.0
10°	2101.3
12.5°	1508.8
15°	1047.6
17.5°	684.4
20°	431.5
22.5°	279.5
25°	192.1
27.5°	135.1
30°	97.2
32.5°	69.8
35°	49.5
37.5°	34.5
40°	24.8
42.5°	18.0
45°	13.5
47.5°	10.5
50°	7.1
52.5°	4.5
55°	3.4
57.5°	2.6
60°	1.9
62.5°	1.5
65°	1.1



TEST NUMBER: P740953
CATALOG NUMBER: LD4D08D010-EU4DR200210IC9030-4LBCSSQMB

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.8
70°		0.4

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)