

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751921

Luminaire Tested: LD4D65D010-EU4DR6055659030-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751921
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR6055659030-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6546.8 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751921

CATALOG NUMBER: LD4D65D010-EU4DR6055659030-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P751921
 CATALOG NUMBER: LD4D65D010-EU4DR6055659030-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																												
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																												
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																												
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75																												
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70																												
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65																												
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61																												
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57																												
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53																												
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	715833
5°	714081
10°	737804
15°	738562
20°	679557
25°	578017
30°	440424
35°	311449
40°	182894
45°	73798
50°	24647
55°	11868
60°	4873
65°	724
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 73798 cd/sqm



TEST NUMBER: P751921

CATALOG NUMBER: LD4D65D010-EU4DR6055659030-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	628.1	9.6
10°-20°	1808.8	27.6
20°-30°	2165.0	33.1
30°-40°	1448.0	22.1
40°-50°	429.3	6.6
50°-60°	61.7	0.9
60°-70°	5.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4601.9	70.3
0°-40°	6049.9	92.4
0°-60°	6541.0	99.9
0°-90°	6546.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6546.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6552	
5°	6511	628
15°	6529	1809
25°	4795	2165
35°	2335	1448
45°	478	429
55°	62	62
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751921

CATALOG NUMBER: LD4D65D010-EU4DR6055659030-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6551.6
2.5°	6543.3
5°	6510.7
7.5°	6599.0
10°	6650.1
12.5°	6640.8
15°	6529.3
17.5°	6266.4
20°	5844.5
22.5°	5338.1
25°	4794.6
27.5°	4182.2
30°	3490.9
32.5°	2873.9
35°	2335.0
37.5°	1795.2
40°	1282.3
42.5°	845.6
45°	477.6
47.5°	244.4
50°	145.0
52.5°	93.8
55°	62.3
57.5°	40.0
60°	22.3
62.5°	9.3
65°	2.8
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)