

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740977

Luminaire Tested: LD4D08D010-EU4DR200210IC9035-4LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P740977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR200210IC9035-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 668.4 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740977
CATALOG NUMBER: LD4D08D010-EU4DR200210IC9035-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P740977

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9035-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	415672
5°	375022
10°	210476
15°	106996
20°	45300
25°	20916
30°	11065
35°	5962
40°	3195
45°	1885
50°	1088
55°	571
60°	371
65°	259
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1885 cd/sqm



TEST NUMBER: P740977

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9035-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.9	40.5
10°-20°	266.7	39.9
20°-30°	87.1	13.0
30°-40°	29.7	4.4
40°-50°	10.0	1.5
50°-60°	3.0	0.4
60°-70°	1.0	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	624.7	93.5
0°-40°	654.4	97.9
0°-60°	667.4	99.8
0°-90°	668.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	668.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3804	
5°	3419	271
15°	946	267
25°	174	87
35°	45	30
45°	12	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P740977
CATALOG NUMBER: LD4D08D010-EU4DR200210IC9035-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3804.4
0.5°	3804.4
1°	3799.7
1.5°	3790.2
2°	3772.9
2.5°	3749.9
3°	3717.4
3.5°	3672.0
4°	3604.6
4.5°	3522.6
5°	3419.3
5.5°	3283.4
6°	3144.2
6.5°	2984.6
7°	2828.4
7.5°	2645.5
8°	2482.2
8.5°	2317.9
9°	2166.1
9.5°	2026.9
10°	1897.1
12.5°	1362.2
15°	945.9
17.5°	617.9
20°	389.6
22.5°	252.4
25°	173.5
27.5°	122.0
30°	87.7
32.5°	63.0
35°	44.7
37.5°	31.2
40°	22.4
42.5°	16.3
45°	12.2
47.5°	9.5
50°	6.4
52.5°	4.1
55°	3.0
57.5°	2.4
60°	1.7
62.5°	1.4
65°	1.0



TEST NUMBER: P740977
CATALOG NUMBER: LD4D08D010-EU4DR200210IC9035-4LBSQW1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.7
70°		0.3

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)