

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752022

Luminaire Tested: LD4D65D010-EU4DR6555659035-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P752022  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D65D010-EU4DR6555659035-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5300.9 lumens  
Efficiency: N/A  
Efficacy: 72.8 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P752022

CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P752022

CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93					93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87					87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80					80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75					75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69					69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65					65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60					60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57					57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53					53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50					50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	570243
5°	570721
10°	590811
15°	591784
20°	544843
25°	464225
30°	355390
35°	251080
40°	148207
45°	60169
50°	21808
55°	12153
60°	6971
65°	3826
70°	4025
75°	3124
80°	3272
85°	2758

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 60169 cd/sqm



TEST NUMBER: P752022

CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	502.6	9.5
10°-20°	1449.6	27.3
20°-30°	1739.3	32.8
30°-40°	1168.9	22.1
40°-50°	349.9	6.6
50°-60°	61.8	1.2
60°-70°	17.6	0.3
70°-80°	8.6	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3691.5	69.6
0°-40°	4860.4	91.7
0°-60°	5272.1	99.5
0°-90°	5300.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5300.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5219	
5°	5204	503
15°	5232	1450
25°	3851	1739
35°	1882	1169
45°	389	350
55°	64	62
65°	15	18
75°	7	9
85°	2	3
90°	0	



TEST NUMBER: P752022

CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5219.1
2.5°	5241.4
5°	5203.6
7.5°	5282.2
10°	5325.2
12.5°	5314.8
15°	5231.7
17.5°	5028.5
20°	4685.9
22.5°	4282.4
25°	3850.7
27.5°	3363.5
30°	2816.9
32.5°	2321.4
35°	1882.4
37.5°	1448.5
40°	1039.1
42.5°	678.6
45°	389.4
47.5°	206.2
50°	128.3
52.5°	89.0
55°	63.8
57.5°	46.0
60°	31.9
62.5°	20.8
65°	14.8
67.5°	13.4
70°	12.6
72.5°	9.6
75°	7.4
77.5°	6.7
80°	5.2
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)